

3M™ Peltor™ HT Series™ Listen-Only Headsets

PELTOR

The Sound Solution

High-performance protection for high-noise environments



With its carefully designed speaker system and excellent attenuation, Peltor™ HT Series™ Listen-Only headsets offer clear sound reproduction and communication in high-noise environments. Peltor's proven and durable designs provide high-comfort levels, allowing long-term use under tough conditions. Possible applications may be found in high-noise industries such as:

- Heavy equipment operators
- Airport workers
- Construction
- Manufacturing
- Agricultural
- Racing
- Oil rigs, petroleum refineries

3M

PELTOR

The 3M™ Peltor™ line of HT Series™ listen-only headsets exhibits the versatility along with the protection, durability and comfort that you expect from a worldwide leader in communication headsets. HT Series industrial headsets feature clear sound reproduction combined with a wide selection of connectors which enable them to be used with speaker microphones, VHF/UHF radios or personal entertainment devices in high-noise areas.



Headband



Neckband



Hard-Hat Mount

Headset
Carrying Bag
FP9007-US

Listen-only headset (mono)

HTM79A	Headband (mono); 3.5mm plug; NRR 25 dB*
HTM79B	Neckband (mono); 3.5mm plug; NRR 24 dB*
HTM79P3E	Hard-Hat Mount (mono); 3.5mm plug; NRR 23 dB*
HTM79A-03	Headband (mono); 2.5mm plug; NRR 25 dB*
HTM79A-25	Headband (mono); 1/4" plug; NRR 25 dB*
HTM79A-42	Headband; 3.5mm threaded plug; Motorola HT1000 or equiv.; NRR 25 dB*
HTM79A-49	Headband; Disconnect Cable Option: FL6* cables sold separately; NRR 25 dB*
HTM79A-CSA	Headband (mono); 3.5mm threaded plug; CSA Intrinsic Safety approval; NRR 25 dB*
HTM79B-03	Neckband (mono); 2.5mm plug; NRR 24 dB*
HTM79B-25	Neckband (mono); 1/4" plug; NRR 24 dB*
HTM79B-42	Neckband; 3.5mm threaded plug; Motorola HT1000; NRR 24 dB*
HTM79B-49	Neckband; Disconnect Cable Option: FL6 cables sold separately; NRR 24 dB*
HTM79B-CSA	Neckband (mono); 3.5mm plug; CSA Intrinsic Safety approval; NRR 24 dB*
HTM79P3E-03	Hard-Hat Mount (mono); 2.5mm plug; NRR 23 dB*
HTM79P3E-25	Hard-Hat Mount (mono); 1/4" plug; NRR 23 dB*
HTM79P3E-42	Hard-Hat Mount; 3.5mm threaded plug; Motorola HT1000; NRR 23 dB*
HTM79P3E-49	Hardhat Mount; Disconnect Cable Option: FL6 cables sold separately; NRR 23 dB*
HTM79P3E-49A	Speaker on one side; NRR 23 dB*
HTM79P3E-CSA	Hard-Hat Mount (mono); 3.5mm plug; CSA Intrinsic Safety approval; NRR 23 dB*
HTM31B	Neckband (mono); 3.5mm plug; Beveled cups; NRR 24 dB*
HTM540A-395-BA	Headband (mono); 3.5mm plug; NRR 27dB*; NRR 27 dB*
HTM540P3E-395-BA	Hard-Hat Mount (mono); 3.5mm plug; NRR 26 dB*

Listen-only headsets for use with portable music or entertainment devices

HTB79A	Headband; stereo; 1/4" plug; NRR 25 dB*
HTB79A-02	Headband; stereo; 3.5mm plug; NRR 25 dB*

*Research indicates that many users will receive less noise reduction than indicated by the NRR due to variation in earplug fit, earplug fitting skill, and motivation of the user. It is recommended that the NRR be reduced by 50% to better estimate typical workplace protection.

Accessories - Additions

FL6M	2.5mm Mono Plug; Straight cable; 36 inches
FL6M-03	2.5mm Mono Plug; Curly cable; 12 inches
FL6H	3.5mm Mono Plug; Straight cable; 36 inches
FL6H-03	3.5mm Mono Plug; Curly cable; 12 inches
FL6N	3.5mm Stereo Plug for Walkman; Straight cable; 36 inches
FL6N-01	3.5mm Threaded Stereo Plug; Curly cable; 36 inches
HY79	Replacement earcushions & foam
HY80	Gel sealing ring (pair)
FP9007-US	Headset carrying bag



**Occupational Health and
Environmental Safety Division**
3M Center
Building 235-2W-70
St. Paul, MN 55144-1000

For More Information
www.3M.com/OccSafety
Technical Assistance (U.S.A.)
1-800-665-2942
Customer Service (U.S.A.)
1-800-328-1667

Please recycle. Printed in U.S.A. Blg 10080929
© 3M 2010. All rights reserved. 3M is a trademark
of 3M Company, used under license in Canada.
Peltor and HT Series are trademarks of 3M
Svenska AB used under license by 3M.
70-0715-7195-7

⚠ WARNING!

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. **Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury.** For proper use, see supervisor, User Instructions, or call 3M in U.S.A. at 1-800-665-2942.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[HTM79P3E](#) [HTM79P3E-CSA](#) [HTM79A](#)