



ASE42GL Product Details



ASE42GL (1-1437581-7)

TE Internal Number: 1-1437581-7

Active

Slide Switches

Always ELV Compliant (Find RoHS Compliant Alternates/Statement of Compliance)

Product Highlights:

- 2 Positions
- Four Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Top
- Actuator Color = Black
- ASE/F Series

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH ASE/ASF, AUTO-INSERTABLE, THRU-HOLE AND...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Dimensional Drawing](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Actuator Style = Extended, Top
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Telecom

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

Termination Features:

- Termination Type = PC

Body Features:

- Actuator Color = Black
- Mount Style = Surface Mount
- Switch Style = Auto-insertable
- Actuator Material = Polyester

Contact Features:

- Contact Plating = Gold
- Contact Base Material = Copper Alloy

Configuration Features:

- [Number of Positions](#) = 2
- Configuration (Pole-Throw) = Four Pole - Double Throw
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C
- RoHS/ELV Compliance History = Always was ELV compliant

Identification Marking:

- Stamped Marking = With

Other:

- Series = ASE/F
- Brand = Alcoswitch

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



Feedback

