




# ASE62GL Product Details

Share Print Email



**ASE62GL**  
(3-1437581-4)

TE Internal Number: 3-1437581-4

Active

## Slide Switches

Always ELV Compliant (Find RoHS Compliant Alternates/Statement of Compliance)

### Product Highlights:

- 2 Positions
- Six Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Top
- Actuator Color = Black
- ASE/F Series

[View all Features](#)

## Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- [SLIDE SWITCH ASE/ASF, AUTO-INSERTABLE, THRU-HOLE AND...](#) (PDF, English)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Additional Product Images:

- [Dimensional Drawing](#)

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Actuator Style = Extended, Top
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Telecom

### Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

### Termination Features:

- Termination Type = PC

### Body Features:

- Actuator Color = Black
- Mount Style = Surface Mount
- Switch Style = Auto-insertable
- Actuator Material = Polyester

### Contact Features:

- Contact Plating = Gold
- Contact Base Material = Copper Alloy

### Configuration Features:

- [Number of Positions](#) = 2
- Configuration (Pole-Throw) = Six Pole - Double Throw
- Number of Actuators = Single

### Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C
- RoHS/ELV Compliance History = Always was ELV compliant

### Identification Marking:

- Stamped Marking = With

### Other:

- Series = ASE/F
- Brand = Alcoswitch

## Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)

## Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)

## Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

## Keep Me Informed



Feedback

