



<b>5 Diopter High Quality Glass Lens</b>  Additional 12 diopter spot lens	<b>18 White LEDs</b> Two intensity levels (4 watt)  <b>26 UV LEDs</b> (8 watt)	<b>Long LED Life</b>  White LEDs: 36,000+ hours UV LEDs: 30,000+ hours	<b>Rechargeable Battery</b> (400 mAh Lithium ion)  UV LEDs: 2 hours White LEDs: Up to 6 hours
--	---	---	--



**18 White LEDs w/ Two Intensity Levels**  
(4 watt)



**26 UV LEDs**  
(8 watt)

# Wide View UV Magnifier

## Hand-Held Magnifier w/ Ultraviolet & White LEDs

Aven's Wide View UV Magnifier features a rectangular high quality glass with UV and White LEDs. Ideal for Dermatology, Trauma, Schools, Ophthalmology, Forensic Science, Hospitality/Food Industry, Agriculture, and Industrial Inspection for detecting defects.

### Key Features

- 5 Diopter (2.25x) high quality glass lens with additional 12 diopter (4x) spot lens
- Bright white LEDs operating at 6500 Kelvin (White LEDs) and UV LEDs operating at 365nm
- 18 White LEDs with two intensity levels (4 watt)
- 26 UV LEDs (8 watt)
- 36,000+ hours (White LEDs) 30,000+ hours (UV LEDs)
- 400 mAh Rechargeable Lithium Ion Battery. Will last 2 hours in UV mode and up to 6 hours in white LED mode. Power adapter included. (1A/5V)
- Device can be used via the power adapter when battery is drained
- ESD Safe

Wide View UV Magnifier	
Hand Held Magnifier w/ Ultraviolet & White LEDs	
<b>Item #</b>	26060
<b>Lens Dimensions</b>	93mm x 43mm Rectangle (3.7 in x 1.7 in)
<b>Magnification</b>	5 Diopter (2.25x) w/ 12 Diopter (4x) Spot Lens
<b>LEDs</b>	<ul style="list-style-type: none"> <li>• 18 White LEDs (6500k)</li> <li>• 26 UV LEDs (365nm)</li> </ul>
<b>Operation</b>	<ul style="list-style-type: none"> <li>• Micro-Touch buttons</li> <li>• 2 Stage brightness intensity for White LEDs</li> </ul>
<b>Battery</b>	400 mAh Rechargeable Lithium Ion Battery
<b>Power Adapter</b>	1A/5V
<b>Package Contents</b>	<ul style="list-style-type: none"> <li>• Wide View Magnifier</li> <li>• Power Adapter/Charger</li> <li>• User Guide</li> </ul>



**Professional  
Inspection**



**Education**



**Reading**



**Home Use**



**Collecting**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aven:](#)

[26060](#)