

# LEGACY THAT FLOWS™

**KLEIN  
TOOLS®**



# LEGACY THAT FLOWS™

Our new line of plumbing tools expands our legacy by delivering next-generation solutions that empower professionals to tackle every challenge. This innovative portfolio reimagines the most frequently used tools, incorporating features that streamline efficiency and enhance performance. The lineup includes Pipe Wrenches, Tubing Cutters, PVC and PEX Cutters, and Appliance Installation Tools.



# PIPE WRENCHES









## PIPE WRENCHES

### TRADITIONAL PIPE WRENCHES

I-Beam design significantly reduces weight in the handle while maintaining durability. This allows for more balanced application and easier handling.

- Optimized jaw design for no-slip grip
- Hang hole for convenient storage
- Adjustable jaws



|               |   |   |   |   |
|---------------|---|---|---|---|
| CAST ALUMINUM | 14"   | 2"  | 18"   | 2-1/2"  |
|               |    |    |    |    |
|               |   | 68224   |   | 68225   |
| CAST IRON     | 14"   | 2"  | 18"   | 2-1/2"  |
|               |  |  |  |  |
|               |   | 68227   |   | 68228   |

### "S-JAW" PIPE WRENCH

Combining the best of channel locks and traditional pipe wrenches.

#### Quick-Adjust "S-Jaw" Pipe Wrench

- 3-points of contact for no-slip grip
- Fast-action button for easy size extension



**KLEIN  
TOOLS**

# TUBING CUTTERS

## QUICK-ADJUST TUBING CUTTER

Innovation buried in a traditional plumber's tool.



### 1-5/8" Quick-Adjust Tubing Cutter

- Fast-action button and ergonomic adjustment knob to adjust cut capacity
- Built-in telescoping deburring tool
- Spare blade stored in knob (Cat. No. 50054)
- Push pin for easy blade replacement

## TRADITIONAL TUBING CUTTERS

Diversifying our portfolio with most commonly used plumber's tools with a broad range of cutting capacities.



### 1-3/8" Constant Swing Tubing Cutter

- Ergonomic adjustment knob to adjust cut capacity
- Built-in telescoping deburring tool
- Spare blade stored in knob (Cat. No. 50054)
- Push pin for easy blade replacement



### 1-1/8" Mini Tubing Cutter


- Ergonomic adjustment knob to adjust cut capacity
- Spare blade stored in knob (Cat. No. 50054)
- Push pin for easy blade replacement



### 5/8" Nano Tubing Cutter

- Compact size for working in low clearance spaces
- Ergonomic adjustment knob to adjust cut capacity
- Push pin for easy blade replacement

# TUBING CUTTERS



**KLEIN  
TOOLS**

# TUBING CUTTERS

## TUBING CUTTERS

### C-STYLE TUBING CUTTERS

Ultra-compact design optimized for working in tight spaces.

- Spring-loaded blade for maintained cutting force
- Water drainage ports to prevent water build up



50057

**1" C-Style  
Tubing Cutter**



50056

**3/4" C-Style  
Tubing Cutter**



50055

**1/2" C-Style  
Tubing Cutter**



50048

**C-Style Tubing  
Cutter 3-Piece Set**

- MODbox™ compatible case (attach to Case Adapter Rail Attachment Cat. No. 54875MB)
- Includes 50055; 50056; 50057

# PVC & PEX CUTTERS

## TRADITIONAL PVC CUTTER



50063

### 1-1/4" Ratcheting PVC Cutter

- Ratcheting ability for easier cutting
- For use with PEX and PVC
- One-handed blade retraction

## PRECISION PVC CUTTER



50044

### 1-1/4" Ratcheting Precision PVC Cutter

- Quick-release button for blade retraction
- Improved ratcheting ability
- Jaw nesting for variety of jaw sizes
- Easy blade exchange

## PEX & SOFT- SHELLED TUBING CUTTER



50043

### 1" PEX & Tubing Cutter

- Pierce-point blade for improved cutting
- Easy blade exchange

# PVC & PEX CUTTERS



**KLEIN  
TOOLS**

# APPLIANCE INSTALLATION



**KLEIN  
TOOLS®**



## 1-1/4" Telescoping Basin Wrench

- Fits around hex nuts up to 1-1/4"
- Spring-loaded jaw design for easier attachment
- Added leverage via screwdriver passthrough and 3/8" square drive connection



## 12-in-1 Faucet Wrench Multi-Tool

- Multi-purpose tool for installing and repairing faucet, toilet, and sink fixtures
- Extends up to 14.5"
- Added leverage via 3/8" square drive connection and screwdriver passthrough



## 3-in-1 Tube Bender

- Fits 1/4", 5/16" and 3/8" O.D. tubing
- Designed for use with soft copper, aluminum, thin wall steel, and thin wall stainless steel tubing
- Up to 180-Degree bends

# REPLACEMENT PARTS



50054

Tubing Cutter Replacement  
Blades, 2-Pack



50058

Replacement Blade for  
50054 PVC Cutter



50060

Replacement Blade for  
50043 PEX & Tubing Cutter

# PRODUCT INFORMATION

## PIPE WRENCHES

| Cat.No. | UPC<br>0-92644+ | Product<br>Description                | Jaw<br>Capacity                            | Special<br>Features                      | Length      | Weight           |
|---------|-----------------|---------------------------------------|--|--|-------------|------------------|
| 68224   | 68224-7         | 14" Cast Aluminum Pipe Wrench         | 2" (5 cm)                                  | I-Beam Handle; Hang Hole; Adjustable Jaw | 14" (35 cm) | 1.9 lb (861.8 g) |
| 68225   | 68225-4         | 18" Cast Aluminum Pipe Wrench         | 2-1/2" (6 cm)                              | I-Beam Handle; Hang Hole; Adjustable Jaw | 18" (46 cm) | 3.3 lb (1.5 kg)  |
| 68227   | 68227-8         | 14" Cast Iron Pipe Wrench             | 2" (5 cm)                                  | I-Beam Handle; Hang Hole; Adjustable Jaw | 14" (35 cm) | 2.9 lb (1.3 kg)  |
| 68228   | 68228-5         | 18" Cast Iron Pipe Wrench             | 2-1/2" (6 cm)                              | I-Beam Handle; Hang Hole; Adjustable Jaw | 18" (46 cm) | 5.2 lb (2.4 kg)  |
| 68230   | 68230-8         | 13" Quick-Adjust S-Jaw<br>Pipe Wrench | Hex: 1-1/4" (3 cm)<br>Round: 1-1/2" (4 cm) | S-Shaped Jaw; Adjustable                 | 13" (33 cm) | 2 lb (907 g)     |

## TUBING CUTTERS

| Cat.No. | UPC<br>0-92644+ | Product<br>Description                      | Cut<br>Capacity                                 | Special<br>Features  | Material          | Reams | Spare Blade<br>Included |
|---------|-----------------|---|---|--|-------------------|-------|-------------------------|
| 50061   | 50061-9         | 1-5/8" Quick-Adjust Tubing Cutter           | 1/8" to 1-5/8"<br>(3 to 41 mm) O.D.             | Spring-Action Button;<br>Contoured Adjustment Knob                       | Copper & Aluminum | Yes   | Yes                     |
| 50046   | 50046-6         | 1-3/8" Constant-Swing Tubing Cutter         | 1/8" - 1-3/8"<br>(3 mm - 35 mm) O.D.            | Contoured Adjustment Knob  | Copper & Aluminum | Yes   | Yes                     |
| 50047   | 50047-3         | 1-1/8" Mini Tubing Cutter                   | 1/8" to 1-1/8"<br>(3 to 28 mm) O.D.             | Contoured Adjustment Knob  | Copper & Aluminum | –     | Yes                     |
| 50049   | 50049-7         | 5/8" Nano Tubing Cutter                     | 1/8" to 5/8"<br>(3 to 28 mm) O.D.               | Contoured Adjustment Knob  | Copper & Aluminum | –     | –                       |
| 50055   | 50055-8         | 1/2" C-Style Tubing Cutter                  | 1/2" (12 mm) I.D.                               | Spring-Action Blade;<br>Water Drainage Ports                             | Copper            | –     | –                       |
| 50056   | 50056-5         | 3/4" C-Style Tubing Cutter                  | 3/4" (1.9 cm) I.D.                              | Spring-Action Blade;<br>Water Drainage Ports                             | Copper            | –     | –                       |
| 50057   | 50057-2         | 1" C-Style Tubing Cutter                    | 1" (2.5 cm) I.D.                                | Spring-Action Blade;<br>Water Drainage Ports                             | Copper            | –     | –                       |
| 50048   | 50048-0         | C-Style Tubing Cutter, 3-Piece              | 1/2"; 3/4"; 1" (1.2 cm;<br>1.9 cm; 2.5 cm) I.D. | MODbox™ Compatible Case;<br>Spring-Action Blade; Water<br>Drainage Ports | Copper            | –     | –                       |
| 50054   | 50054-1         | Tubing Cutter Replacement<br>Blade, 2-Piece | –   | –  | Copper & Aluminum | –     | –                       |

## PVC & PEX CUTTERS

| Cat.No. | UPC 0-92644+ | Product Description                       | Cut Capacity        | Special Features  | Material                     | Ratcheting |
|---------|--------------|---|---------------------|---|------------------------------|------------|
| 50063   | 50063-3      | 1-1/4" Ratcheting PVC Cutter              | 1-1/4" (31 mm) I.D. | Locking Latch; Retracting Blade   | PVC and PEX                  | Yes        |
| 50044   | 50044-2      | 1-1/4" Precision Ratcheting<br>PVC Cutter | 1-1/4" (31 mm) I.D. | Locking Latch; Blade Retracting<br>Button; Pierce-Point Blade;<br>Versatile Jaw Shape | PVC and PEX                  | Yes        |
| 50043   | 50043-5      | 1" PEX & Tubing Cutter                    | 1" (25 mm) I.D.     | Locking Latch; Pierce-Point Blade   | PEX and Soft-Shell ed Tubing | –          |

## APPLIANCE INSTALLATION

| Cat.No. | UPC 0-92644+ | Product Description              | Capacity   | Special Feature   | Length                  | Weight            |
|---------|--------------|----------------------------------|--|---|-------------------------|-------------------|
| 51006   | 51006-9      | 3-in-1 Tubing Bender             | 1/4", 5/16", 3/8" O.D.   | Bends three common tubing sizes   | 10.5" (26.7 cm)         | 13.7 oz (388.4 g) |
| 68232   | 68232-2      | 1-1/4" Telescoping Basin Wrench  | 1-1/4" Hex Nuts  | Spring-Action Jaw; Adjustable Handle;<br>Screwdriver Passthrough; 3/8" Square<br>Drive Connection   | 10-17" (24.4 – 43.2 cm) | 1.8 lb (0.8 kg)   |
| 68098   | 68098-4      | 12-in-1 Faucet Wrench Multi-Tool | Tab Mount: 2, 3, 4, 6;<br>Hex Nut: 15/16"; 3/4";<br>7/8"; 5/8" | Tab Mount Wrench; Valve Wrench; Hex<br>Nut Wrench; Aerator Wrench; Strainer<br>Wrench; Screwdriver Passthrough; 3/8"<br>Square Drive Connection | 14" (35 cm)             | 2.9 lb (1.3 kg)   |



**KLEIN®  
TOOLS**

See our complete line of **Plumbing Products**

[www.kleintools.com](http://www.kleintools.com)



© 2024 Klein Tools, Inc.  
Lincolnshire, IL 60069  
Rev. 12/24 A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[68224](#) [68228](#) [68230](#) [68225](#) [68227](#) [50043](#) [50048](#) [50044](#) [50055](#) [50056](#) [50057](#) [68098](#) [68232](#)