





- ALL NON-REFERENCE DIMENSIONS ARE REQUIRED
- USE INDEX A, BLACK SEALED AND UNSEALED FOR ALL AFFECTED INSULATOR CAVITIES
 - CURRENT PRODUCTION TOOLING
 - POINT OF LAST RUN
- SERVICE TOOLING GUIDE INFORMATION PER APEX TRAINING MANUAL
-  MUST CONFORM TO THE FOLLOWING CHRYSLER/YNA STANDARDS:
- SAE/USCAR-2 REV.5
 - PF-7300 QUALITY ASSURANCE (CHRYSLER)
 - MS-9502 SEAL APPL. 150 °C
 - MS-8288 SEAL APPL. 125 °C
 - PS-9227 DATA EXCHANGE (CHRYSLER), (G0C9-7 YNA)
 - PS-10052 INFORMATION SECURITY (CHRYSLER)
-  THIS DRAWING (H59011) REPLACED CHRYSLER DRAWING 56038161 REV G
- SUPPLIER CODE FOR MVI : 52772 OR 52772H

REQUIRED			REQUIRED			CLASS 3			ITEM	PART NAME (MATERIAL)	INDEX	CLASS 4			REQUIRED					
						MVL	DELPHI	COLOR				MVL	DELPHI	COLOR						
I			I			I	I	54200327	15537478	BLACK	①	INSULATOR (PA66 GF)	A	54200342	33512049	DK GREEN	I			
	I					I		54200328	15537479	LT GREY	①	INSULATOR (PA66 GF)	B	F974110	33512048	DK BLUE		I		
		I					I	54200329	15537482	DK GREY	①	INSULATOR (PA66 GF)	C	F084110	33512047	DK BROWN			I	
			I					54200330	15537485	NATURAL	①	INSULATOR (PA66 GF)	D							
I	I	I	I	I	I	I	I	54200318	15537469	RED	②	WEDGE (TPA) (PA66 GF)		54200366	33512050	NATURAL	I	I	I	
			I	I	I	I		54200332	15537490	LT BLUE	3A	END SEAL (SILICONE)		54200364	15537497	DK BLUE			I	
						I	I	54200336	15537493	YELLOW NO HOLES	3B	END SEAL (SILICONE)								
							I	54200316	15537464	BLACK	④	RETAINER (PA66 GF)		54200365	15537498	NATURAL	I	I	I	
							I	(ITW DELTAR P/N 15-002775)	CHRYSLER 04625797	BLACK	⑤	SQL X-WAS TREE (CLIP (PA66 GF))								
3	3	3	3	3	3	3	3	CONNECTOR ASSEMBLY TEMPERATURE CLASS PER SAE/USCAR-2 REV 5										4	4	4

CHART-ASSEMBLY PART NUMBERS SEALED			
MVL		DELPHI	
PART NO.	REV	PART NO.	REV
54200354	A	33500096	01
F574110	A	33511485	01
F674110	A	33511486	01

LEGENDS:

C	-	CHRYSLER
F	-	FORD
GM	-	GENERAL MOTORS
MVL	-	MOTORIZED VEHICLES DIVISION
YNA	-	YAZAKI NORTH AMERICA

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15435333](#)