





ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33285119	01	CODE A	ALL PARTS VO / 19,55
33341146	01	CODE B	
33341398	01	CODE C	
33341399	01	CODE D	
33346221	01	CODE A	ALL PARTS NVO / 19,0
33347788	01	CODE B	
33347816	01	CODE C	
33347802	01	CODE D	



POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33282971	33344858	33283284	33295345	33295344	33295343	33346023	33347470	33347469	33347467	33283921	33282492	33344866	33282491	33344853
-	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
-	1	---	1	---	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	1	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	1	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	---	1	---	---	---	---	1	1	---	1	---
-	---	1	---	---	---	---	1	---	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	1	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	1	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	---	1	1	---	1	---	1

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
19NO18	R	01				INITIAL RELEASE		P.BAL	P.NAJ	M.GRU
14MR19	R	01	AA		B6	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
28OC20	R	01	AB		G11	PART AVAILABILITY FOR PART NUMBERS 33346221, 33347788, 33347816, 33347802 UPDATED		P.NAJ	M.GRU	

CLOSED POSITION



SCALE
1:1



NOTES	
-	ON MAIN VIEW ASSEMBLY 33285119 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
-	35269106-CUS71 - PRELIMINARY ASSEMBLY
-	35269106-CUS72 - HARNESS ASSEMBLY
-	35269103-CUS73 - CAR ASSEMBLY
-	35269102-CUS73 - CAR ASSEMBLY
MATING PARTS:	
-	2 WAY 6.3 MALE PANEL MOUNT ASM DWG-NO.: 35153946
-	2 WAY 6.3 MALE STRAP MOUNT ASM DWG-NO.: 35153948
-	BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CSG)
-	BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CSG)
-	PROTECTION CAP APTIV DWG-NO.: 35149886 (HT DWG-NO.: 17-2266-001-CSG)
MATING TERMINAL SYSTEM:	
-	6.3 TERMINAL DWG-NO.: 13976112
-	MAX WIRE CROSS SECTION: 6.0MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

DIM TO CHECK		DIMENSIONAL RANGE (MM)										CHART	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400			
TO	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400				
TOLERANCE UNLESS OTHERWISE SPECIFIED													
ANGULAR TOLERANCE ±2°													
THEORETIC DIM													

DWG TYP		PART DRAWING	
WEIGHT (G)		DISTR CODE	
SEE CHART			
VOLUME (CM ³)			
ROUTING			
UNLESS OTHERWISE SPECIFIED			
GENERAL TOLERANCES ACCORDING TO:			
SEE CHART			
GD&T ACCORDING TO:			
ISO 1101			
REFERENCE			
FIRST ANGLE PROJECTION			
DO NOT SCALE			
USE MATH DATA			

• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAŻNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	DATE
P.BALAJI	18NO18
P.NAJDUCH	19NO18
M.GRUDZEWSKI	20NO18
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIJE PRZETWORZONE OKREŚLA APTIV 10949001

MATERIAL
SEE CHART

DRAWING NAME

2 WAY 6.3
CTCS FEMALE ASSEMBLY

DRAWING NUMBER

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33341399](#)