



ECHELLE 1:1
SCALE 1:1

N°	DESIGNATION	MATIERE / MATERIAL	COULEUR / COLOUR	REF. MVL	REF. APTIV
1	ETRIER / SLIDER	PBT 15% GF	BLEU / BLUE	211 M 6 135	33508065
2	MODULE TERMINAL CARRIER	PBT 0%	NOIR / BLACK	211 I 0 082	33505860
3	PORTE MODULE FEMALE HOUSING	PBT 15%	JAUNE / YELLOW	211 I 4 081	33505882
			ORANGE	211 I 3 081	33505881
			ROUGE / RED	211 I 2 081	33505879
			ROSE / PINK	211 I R 081	33505880

ROUGE / RED	ORANGE	JAUNE / YELLOW	ROSE / PINK	COULEUR / COLOUR
211 PC 20 9 S 2 055	211 PC 20 9 S 3 055	211 PC 20 9 S 4 055	211 PC 20 9 S R 055	REF. MVL
E	E	E	E	IND. / REV.
10866581	13677058	10847065	13985308	REF. APTIV
03	03	03	03	IND. / REV.

CODAGE JAUNE REPRESENTE
YELLOW CODING SHOWN

DWG STATUS				REVISION HISTORY				AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P/CHG	ZONE							
270C17	R	01	-	-	FILE TRANSLATED FROM MVL SYSTEM REDRAWN IN NX			V.K	L.ETF	L.ETF	
03DE18	R	02	-	-	UPDATED TO APTIV STANDARD APTIV P/N ADDED SLIDER MATERIAL UPDATED MVL AND APTIV REVISION LEVEL UPDATED PART LEVEL WAS D			A.RAJ	L.LAU	L.LAU	
18NO20	R	02	AA	-	DISTR CODE "D" WAS "L"			P.BAL	J.LAL	L.LEC	

3D VIEW

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO: ±0.1 ±2°

GD&T ACCORDING TO: ISO 1101

CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.

LA LIGNE TRACÉE SUR LA RÉFÉRENCE PIÈCE INDIQUE QUE LA PIÈCE N'EST PAS DISPONIBLE À LA COMMANDE.

LES RÉFÉRENCES PIÈCES QUI NE SONT PAS BARRÉES INDICENT QUE CELLES-CI SONT DISPONIBLES PHYSIQUEMENT POUR ÊTRE COMMANDEES.

CONTACTER LE SERVICE COMMERCIAL DE APTIV POUR S'ASSURER DE LA DISPONIBILITÉ DES PIÈCES.

R 0.2 MAX SHARP CORNER TOLERANCE

R 0.1 MAX

DO NOT SCALE

USE MATH DATA

DATE TO CHECK COTES A VERIFIER () DIM FOR HELP COTES POUR INFO

THEORETIC DIM COTES THEORIQUES

DWG TYP	PART DRAWING	DISTR CODE
WEIGHT (GR)		
VOLUME (CM ³)		
ROUTING		

REFERENCE: 211P0434

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

• APTIV •

CONNECTION SYSTEMS
Chennai, India

COPYRIGHT 2013 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

CE PLAN EST LE PROPRIÉTAIRE DE APTIV ET CONTIENT DES INFORMATIONS APTIV CONFIDENTIELLES. LA REPRODUCTION, LA DISTRIBUTION ET L'UTILISATION DE CE DOCUMENT OU DE SES DONNÉES MATHÉMATIQUES CAO, AINSI QUE LA COMMUNICATION DE TOUT CONTENU À AUTRUI, SANS AUTORISATION EXPRESSE EST INTERDITE.

DR	T-Piocelle	DATE
APVD1	F FAURIE	19JN02
APVD2	S LACOTE	15JL13
APVD3	L ETIFIER	15JL13
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 MATIERES PROSCRITES ET CONTENU RECYCLABLE SELON APTIV 10949001

MATERIAL SEE TABLE

DRAWING NAME: FEMALE HOUSING 20W HYBRID CONNECTOR

DRAWING NUMBER: 13588409

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	02	AA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[10847065](#)