

Meets ANSI/ESD S20.20 and Packaging standard ANSI/ESD S541



## FEATURES:

- Provides physical protection with conductive material providing reliable path-to-ground
- Includes steel wire frame for extra strength
- No tooling costs
- Easy assembly without the need for tape, glue, or staples
- Ships flat, knocked down
- Available options include: Lid manufactured from Plastek™, ESD Handles, Static Dissipative Foam bottom to provide ESD and shock protection, and Document Holders
- Made in United States of America



Made in the  
United States of America

## SPECIFICATIONS:

### Properties

Properties	Typical Values
Resin Type:	Polypropylene
Conductive:	Inherently
Surface Resistance:	1 x 10 <sup>2</sup> to < 1 x 10 <sup>5</sup> ohms, tested per ANSI/ESD STM11.11
Humidity Independent:	Yes
Temperature Tolerance:	-17°F to +230°F
Melting Point:	324°F

Per Packaging standard ANSI/ESD S541 section 6.1 Inside an ESD Protected Area "Packaging used within an EPA (that satisfies the minimum requirements of ANSI/ESD S20.20) shall be: 1. Low charge generation. 2. Dissipative or conductive materials for intimate contact."

Unless specified tolerance is ± 10%

Part #	REF #	Box Size - L x W x D (IN)	Box Size - L x W x D (MM)	Lid
<a href="#">39300</a>	CPS436-SS	17 x 13 x 6 3/4	432 x 330 x 171	<a href="#">39130</a>
<a href="#">39301</a>	CPS438-SS	17 x 13 x 8 3/4	432 x 330 x 222	<a href="#">39130</a>
<a href="#">39302</a>	CPS439-SS	17 x 13 x 10 3/4	432 x 330 x 273	<a href="#">39130</a>
<a href="#">39303</a>	CPS403-SS	17 x 13 x 12 5/8	432 x 330 x 321	<a href="#">39130</a>
<a href="#">39304</a>	CPS452-SS	18 3/8 x 12 3/8 x 12 3/4	467 x 314 x 324	<a href="#">39132</a>
<a href="#">39306</a>	CPS405-SS	18 3/8 x 12 3/8 x 18 3/4	467 x 314 x 476	<a href="#">39132</a>
<a href="#">39307</a>	CPS406-SS	18 5/8 x 15 x 5 7/8	473 x 381 x 149	<a href="#">39133</a>
<a href="#">39308</a>	CPS468-SS	18 5/8 x 15 x 8	473 x 381 x 203	<a href="#">39133</a>
<a href="#">39309</a>	CPS460-SS	18 5/8 x 15 x 10	473 x 381 x 254	<a href="#">39133</a>
<a href="#">39312</a>	CPS446-SS	22 7/8 x 12 7/8 x 6	581 x 327 x 152	<a href="#">39131</a>
<a href="#">39313</a>	CPS448-SS	22 7/8 x 12 7/8 x 8	581 x 327 x 203	<a href="#">39131</a>
<a href="#">39314</a>	CPS440-SS	22 7/8 x 12 7/8 x 10	581 x 327 x 254	<a href="#">39131</a>

### Built to Order Item List

<a href="#">39305</a>	CPS457-SS	18 3/8 x 12 3/8 x 17 1/8	467 x 314 x 435	<a href="#">39132</a>
<a href="#">39310</a>	CPS462-SS	18 5/8 x 15 x 12	473 x 381 x 305	<a href="#">39133</a>
<a href="#">39311</a>	CPS464-SS	18 5/8 x 15 x 14	473 x 381 x 356	<a href="#">39133</a>
<a href="#">39315</a>	CPS404-SS	22 7/8 x 12 7/8 x 12 5/8	581 x 327 x 321	<a href="#">39131</a>
<a href="#">39316</a>	CPS445-SS	22 7/8 x 12 7/8 x 15 1/4	581 x 327 x 387	<a href="#">39131</a>
<a href="#">39317</a>	CPS408-SS	22 7/8 x 12 7/8 x 18 1/4	581 x 327 x 464	<a href="#">39131</a>

Specifications and procedures are subject to change without notice.

## Plastek™ Shipper Saver Storage Container

PROTEKTIVE PAK  
13520 MONTE VISTA AVENUE, CHINO, CA 91710  
PHONE (909) 627-2578  
[ProtektivePak.com](http://ProtektivePak.com)

DRAWING NUMBER

39300

DATE

July  
2016

# PROTEKTIVE PAK

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Desco:](#)

[39313](#) [39315](#) [39317](#) [39311](#) [39300](#) [39305](#) [39310](#) [39316](#) [39308](#) [39302](#) [39312](#) [39301](#) [39314](#) [39304](#)