




Made in America



- A. Black ABS plastic cap. Molded with DESCO's name and part number.
  - B. 300 series stainless steel backplate (0.015" thick). Manufacturing date code is stamped into stainless steel back plate.
  - C. Two 4mm snap studs machined from 300 series stainless steel. Fits to 4mm spring loaded medical type socket. Coil cord disengages from snap with 1-5 lbs. of perpendicular force. Durable, providing long life well beyond that of sheet metal snaps.
  - D. Premium metal expansion wrist strap. Inside links are constructed of 300 Series Stainless Steel. Width of links is 0.630".
  - E. .002" polyphenylsulfone sheet is laminated to each link before assembly. Provides >5,000 volt RMS insulation per ASTM D149. Will not flake or peel.
  - F. Black ABS plastic insulator separates band into halves.
  - G. Underwriters' Laboratory listed 90P1C.
- Meets or exceeds requirements of EOS/ESD-S1-1987.

ITEM	DESCRIPTION	CIRCUMEFERENCE		WIDTH
		MIN	MAX	
<a href="#">19844</a>	Premium Metal Expansion Wristband only, S	5.5" (140mm)	9" (229mm)	0.630"
<a href="#">19842</a>	Premium Metal Expansion Wristband only, M	6" (152mm)	11" (279mm)	0.630"
<a href="#">19840</a>	Premium Metal Expansion Wristband only, L	7" (178mm)	12" (305mm)	0.630"
<a href="#">09165</a>	Premium Metal Expansion Wrist Strap Kit, with 6' Coil Cord, right angle mono plug, S	5.5" (140mm)	9" (229mm)	0.630"
<a href="#">09166</a>	Premium Metal Expansion Wrist Strap Kit, with 6' Coil Cord, right angle mono plug, M	6" (152mm)	11" (279mm)	0.630"
<a href="#">09167</a>	Premium Metal Expansion Wrist Strap Kit, with 6' Coil Cord, right angle mono plug, L	7" (178mm)	12" (305mm)	0.630"
<a href="#">09168</a>	Premium Metal Expansion Wrist Strap Kit, with 12' Coil Cord, right angle mono plug, S	5.5" (140mm)	9" (229mm)	0.630"
<a href="#">09169</a>	Premium Metal Expansion Wrist Strap Kit, with 12' Coil Cord, right angle mono plug, M	6" (152mm)	11" (279mm)	0.630"
<a href="#">09170</a>	Premium Metal Expansion Wrist Strap Kit, with 12' Coil Cord, right angle mono plug, L	7" (178mm)	12" (305mm)	0.630"

Specifications and procedures subject to change without notice.

Unless otherwise noted, tolerance  $\pm 10\%$

\*U.S. Patents 6,052,053 and 6,205,408

See Drawing [09160](#) for details on Jewel® Coil Cords

### Jewel® Premium Metal Expansion Dual Wire Wrist Strap, 4mm

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: [Desco.com](http://Desco.com)  
PHONE (909) 627-8178 FAX (909) 627-7449

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407  
PHONE (781) 821-8370 FAX (781) 575-0172

DRAWING NUMBER  
09165

DATE:  
April  
2011

# DESCO

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Desco:](#)

[09167](#) [09168](#) [09169](#)