

Box terminal TS1.5 3 units 35...300 mm² accessories for: 3VA1 400/630 3VA2 400/630



Model	
product brand name	SETRON
product designation	accessories
design of the product	box terminal 3 units
accessories	Box terminal
General technical data	
designation / of the terminal	TS1.5
type of electrical connection / with control wire tap	No
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	35 mm ²
• for copper cable / stranded / maximum	300 mm ²
type of connectable conductor cross-sections / of the laminated conductor rails	
• minimum	2 - 10x 20 mm x 1 mm
• maximum	2 - 10x 24 mm x 1 mm
stripped length	26.5 mm
tightening torque / when using copper cables	
• stranded	35 - 95 mm ² : 16 Nm, 120 - 300 mm ² : 28 Nm
• finely stranded	35 - 95 mm ² : 16 Nm, 120 - 240 mm ² : 28 Nm
Connections according UL	
stripped length	1.05 in
connectable conductor cross-section	
• for copper cable / stranded / minimum	1/0 AWG
• for copper cable / stranded / maximum	500 kcmil
• for copper cable / finely stranded / minimum	1/0 AWG
• for copper cable / finely stranded / maximum	500 kcmil
• for copper cable / finely stranded / with core end processing / minimum	1/0 AWG
• for copper cable / finely stranded / with core end processing / maximum	500 kcmil
tightening torque / when using copper cables	
• stranded	1/0 - 4/0: 140 lb-in 250 -500 kcmil: 248 lb-in
• finely stranded	1/0 - 4/0: 140 lb-in 250 -500 kcmil: 248 lb-in
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9483-0JA13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9483-0JA13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9483-0JA13

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/19/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA94830JA13](#)