



Integrated signal lamp, rotating light, with integrated LED, red, 24 V AC/DC, Diameter 70 mm

General technical data			
product designation	Rotating light element		
consumed current maximum	40 mA		
type of voltage of the operating voltage	AC/DC		
operating voltage			
• 1 at DC rated value			24 V
• 1 at AC at 50 Hz rated value			24 V
• 1 at AC at 60 Hz rated value			24 V
relative positive tolerance of the operating voltage	10 %		
relative negative tolerance of the operating voltage	-10 %		
speed	120 1/min		
reference code according to IEC 81346-2	P		
fastening method	Bayonet / flush mounting		
material	PC; PC/ABS; PA		
color	red		
Mechanical data			
product component light source	Yes		
type of electrical connection	screw-type terminals		
outer diameter of the signal column element	75 mm		
Lamp			
design of the optical signal	rotating light		
type of light source	LED		
light intensity	2.8 cd		
service life of LED	100 000 h		
Ambient conditions			
ambient temperature during operation	-20 ... +50 °C		
protection class IP	IP65		
depth	31 mm		
height	66 mm		
width	75 mm		
Certificates/ approvals			
General Product Approval	EMC	Declaration of Conformity	

[Confirmation](#)



other

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5320-5DB>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5320-5DB>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD5320-5DB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5320-5DB&lang=en





last modified:

12/23/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

8WD53205DB