





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product Compatibility	XCKJ
Associated lever	ZCKY43 ZCKY81 ZCKY11 ZCKY14 ZCKY13 ZCKY41 ZCKY51 ZCKY52 ZCKY53 ZCKY59 ZCKY91
Associated body	ZCKJD35H7 ZCKJ21 ZCKJ2H29 ZCKJ4H29 ZCKJD37H7 ZCKJD35H29 ZCKJ41 ZCKJ21H7 ZCKJ4H7 ZCKJD31 ZCKJ404H29 ZCKJ8H7 ZCKJ5H29 ZCKJ9H7 ZCKJD39H7 ZCKJ1H7 ZCKJD31H29 ZCKJ4104 ZCKJ9H29 ZCKJ6 ZCKJ6H29 ZCKJ8H29 ZCKJ7H7 ZCKJD39 ZCKJ6H7 ZCKJ404H7 ZCKJD37H29 ZCKJ41H29 ZCKJ9 ZCKJ11H7 ZCKJ7H29 ZCKJ2 ZCKJD37 ZCKJ404 ZCKJ4104H7 ZCKJ21H29 ZCKJ7 ZCKJ5H7 ZCKJD31H7 ZCKJ4104H29 ZCKJ8 ZCKJ5 ZCKJD35 ZCKJ1H29 ZCKJ1 ZCKJ41H7 ZCKJ11 ZCKJ4 ZCKJD39H29 ZCKJ2H7 ZCKJ11H29
Movement of operating head	Rotary

Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Switch actuation	From left and/or right CW and/or CCW
Positive opening	With
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Corrosive

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110599367
Nbr. of units in pkg.	1
Package weight(Lbs)	6.17 oz (175.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.65 in (4.2 cm)
Package 1 width	1.77 in (4.5 cm)
Package 1 Length	3.43 in (8.7 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Weight	5.78 lb(US) (2.622 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE05TK](#)