

# ZCKE615

Limit switch head, Limit switches XC Standard, ZCKE, metal end plunger, +120 °C



## Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJD37H29 ZCKJ21 ZCKJD39H29 ZCKJ1 ZCKJ4 ZCKJD31 ZCKJ8H7 ZCKJ4H7 ZCKJD31H7 ZCKJ11H29 ZCKJD35 ZCKJ2 ZCKJ41H29 ZCKJ9H29 ZCKJ41 ZCKJ11H7 ZCKJ6H29 ZCKJD39H7 ZCKJD37 ZCKJ9 ZCKJ21H29 ZCKJ4H29 ZCKJ5 ZCKJ8H29 ZCKJD31H29 ZCKJ11 ZCKJD37H7 ZCKJ41H7 ZCKJD35H29 ZCKJ5H7 ZCKJ21H7 ZCKJ5H29 ZCKJ1H29 ZCKJ7H7 ZCKJ6H7 ZCKJD35H7 ZCKJ2H7 ZCKJ9H7 ZCKJ7 ZCKJ8 ZCKJ1H7 ZCKJD39 ZCKJ7H29 ZCKJ6 ZCKJ2H29
Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

## Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

## Environment

Ambient Air Temperature for Operation	50...248 °F (10...120 °C)
Ambient Air Temperature for Storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

## Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110599435
Nbr. of units in pkg.	1
Package weight(Lbs)	5.04 oz (142.9 g)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.61 in (4.1 cm)
Package 1 width	1.77 in (4.5 cm)
Package 1 Length	3.35 in (8.5 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Weight	4.85 lb(US) (2.202 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE615](#)