

ZCKE61TK

Limit switch head, Limit switches XC Standard, ZCKE, metal end plunger



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJD37H7 ZCKJD35H7 ZCKJ8 ZCKJ11H7 ZCKJD31H7 ZCKJ7H29 ZCKJ2H29 ZCKJ41 ZCKJ7H7 ZCKJ11H29 ZCKJ2 ZCKJ4H29 ZCKJ8H29 ZCKJD35H29 ZCKJ1 ZCKJ2H7 ZCKJD39H7 ZCKJ7 ZCKJ4H7 ZCKJ5H29 ZCKJD31 ZCKJ1H29 ZCKJ9H7 ZCKJD37 ZCKJD35 ZCKJD37H29 ZCKJ21 ZCKJ5H7 ZCKJ21H7 ZCKJD31H29 ZCKJD39H29 ZCKJ41H7 ZCKJ41H29 ZCKJ21H29 ZCKJ1H7 ZCKJ6 ZCKJ9 ZCKJ8H7 ZCKJ11 ZCKJ4 ZCKJD39 ZCKJ6H29 ZCKJ5 ZCKJ9H29 ZCKJ6H7
Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Corrosive

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110932959
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	3.35 in (8.5 cm)
Package 1 Weight	4.94 oz (140.0 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE61TK](#)