

ZCKD49

Limit switch head, Limit switches XC Standard, ZCKD, thermoplastic roller lever Ø 50 mm variable length



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product Compatibility	XCKS
Associated body	ZCKSD39H29 ZCKS1 ZCKS2 ZCKSD39 ZCKSD31 ZCKS8H29 ZCKS7 ZCKS2H29 ZCKS7H29 ZCKSD35H29 ZCKS8 ZCKS9 ZCKS6 ZCKS6H29 ZCKSD37H29 ZCKSD37 ZCKS1H29 ZCKS5H29 ZCKS5 ZCKS9H29 ZCKSD35 ZCKSD31H29
Movement of operating head	Rotary
Type of operator	Roller lever spring return elastomer adjustable and roller diameter 50 mm)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	Without
Head material	Plastic

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416-LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	3389110774900
Nbr. of units in pkg.	1
Package weight(Lbs)	4.41 oz (125.0 g)

Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.09 in (5.3 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	5.91 in (15 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	11
Package 2 Weight	3.71 lb(US) (1.681 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKD49](#)