

ZCKE619

Limit switch head, Limit switches XC Standard, ZCKE, metal end plunger with protective boot



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJ5 ZCKJD37H7 ZCKJD35 ZCKJ4H29 ZCKJ41H29 ZCKJ21 ZCKJ1 ZCKJD39H29 ZCKJ4 ZCKJ6 ZCKJ11H29 ZCKJ1H29 ZCKJ9 ZCKJ11 ZCKJ7H29 ZCKJ5H29 ZCKJ2H7 ZCKJD39H7 ZCKJ8H29 ZCKJ9H29 ZCKJ1H7 ZCKJD31H29 ZCKJD35H7 ZCKJ41 ZCKJD31 ZCKJD35H29 ZCKJ9H7 ZCKJD39 ZCKJ21H29 ZCKJ11H7 ZCKJ21H7 ZCKJ2H29 ZCKJ6H29 ZCKJ4H7 ZCKJ7H7 ZCKJ5H7 ZCKJ7 ZCKJ8 ZCKJD37 ZCKJ2 ZCKJD31H7 ZCKJ6H7 ZCKJ41H7 ZCKJD37H29 ZCKJ8H7
Movement of operating head	Linear
Type of operator	End plunger spring return metal with protective boot)
Type of approach	Vertical approach, 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110388732
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.73 in (4.4 cm)
Package 1 Width	1.89 in (4.8 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	5.47 oz (155.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	5.17 lb(US) (2.346 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE619](#)