

# ZCKE67TK

Limit switch head, Limit switches XC Standard, ZCKE, steel roller plunger reinforced



## Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJ1 ZCKJ1H29 ZCKJD35H29 ZCKJ4H7 ZCKJ8H7 ZCKJ2 ZCKJ9H29 ZCKJ5H29 ZCKJ8 ZCKJ8H29 ZCKJD39H29 ZCKJ4H29 ZCKJ5 ZCKJ6H7 ZCKJD37H29 ZCKJD35 ZCKJD39H7 ZCKJ2H7 ZCKJD31H7 ZCKJD37H7 ZCKJ11 ZCKJ7H29 ZCKJ11H29 ZCKJ6 ZCKJ41 ZCKJ9 ZCKJD35H7 ZCKJ1H7 ZCKJ41H29 ZCKJ41H7 ZCKJ7 ZCKJD37 ZCKJ6H29 ZCKJ5H7 ZCKJD31 ZCKJ21 ZCKJD39 ZCKJ11H7 ZCKJD31H29 ZCKJ9H7 ZCKJ2H29 ZCKJ21H29 ZCKJ21H7 ZCKJ7H7 ZCKJ4
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal reinforced)
Type of approach	Lateral approach, 2 directions

## Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

## Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Corrosive



## Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110325416
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	3.35 in (8.5 cm)
Package 1 Weight	5.71 oz (162.0 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE67TK](#)