

CY SERIES

SCREW TERMINAL BLOCKS

MULTIPLE CONNECTION TERMINAL BLOCKS


HIGHLIGHTS

FEATURES

- 3 to 4 connections
- Up to 2 connection points on each side
- 2 jumper channels for individual potential distribution

APPLICATIONS

- Connecting different type of wires with different wire sizes into single Terminal Block
- Simple distribution applications



Dimensions & Weight

	CY4/3	CY4/4
Width	6 mm	6 mm
Length	58.8 mm	58.8 mm
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm	50.7 mm 58.2 mm
Weight per piece	12.0 g	14.0 g

Technical Data/Ratings

Approvals				
Wire Size (solid / stranded)	24-10 AWG	0.2-2.5 mm ²	24-10 AWG	0.2-4 mm ²
Voltage Rating	600 V	1000V AC/DC	600 V	1000V AC/DC
Current Rating	30 A	32 A	30 A	32 A
Torque	4.5 lb-in	0.8 Nm	4.5 lb-in	0.8 Nm
Insulation Material	Polyamide 66		Polyamide 66	

Installation Instructions

Wire Stripping Length	9 mm	9 mm
Screwdriver	Flat Head 0.6 x 3.5 mm	Flat Head 0.6 x 3.5 mm

Terminal Blocks

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Grey (standard)	CY4/3	100	CY4/4	100
Red R	CY4/3/R	100	CY4/4/R	100
Blue BU	CY4/3/BU	100	CY4/4/BU	100
Black BL	CY4/3/BL	100	CY4/4/BL	100
Orange O	CY4/3/O	100	CY4/4/O	100
Green G	CY4/3/G	100	CY4/4/G	100
Yellow Y	CY4/3/Y	100	CY4/4/Y	100
White W	CY4/3/W	100	CY4/4/W	100

Accessories

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
End Plate	EPCY4/3	50	EPCY4/4	50
DIN Rail	2511120	20	2511120	20
	CA701-15/S	20	CA701-15/S	20
End Stop	CA702	50	CA702	50
	CA802	50	CA802	50
	CA103	50	CA103	50
Shorting Link/ Jumpers	JX4/2	100	JX4/2	100
	JX4/3	50	JX4/3	50
	JX4/4	50	JX4/4	50
	—	—	—	—
	—	—	—	—
	—	—	—	—
	JX4/8	50	JX4/8	50
	JX4/10	10	JX4/10	10
	JX4/16	10	JX4/16	10
Marking Tag	MT6	1 Pk. (100 tags)	MT6	1 Pk. (100 tags)
Warning Label	WLX4	1 Pk. (100 tags)	WLX4	1 Pk. (100 tags)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CY4/4](#)