

Han M Hood Coupler 1 Lever PG 11



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 37 003 1750 |
| Specification | Han M Hood Coupler 1 Lever PG 11 |
| HARTING eCatalogue | https://b2b.harting.com/09370031750 |

Identification

| | |
|--------------------------|------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] M |
| Type of hood/housing | Cable to cable housing |

Version

| | |
|----------------------|---------------------------------------|
| Size | 3 A |
| Version | Top entry |
| Cable entry | 1x Pg 11 |
| Locking type | Single locking lever |
| Field of application | Hoods/housings for rough environments |
| Pack contents | With seal screw |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP44 IP65 With seal screw IP67 With seal screw |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (locking) | Stainless steel |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|----------------------------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R1 (HL 1-3) R7 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--------------|
| Approvals | CE DNV GL |
|-----------|--------------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 74 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |
| GTIN | 5713140055254 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09370031750](#)