



Pushing Performance  
Since 1945

# HARTING PFT 7\_8 inch male 3-pole



Image is for illustration purposes only. Please refer to product description.

Part number	21 04 316 1305
Specification	HARTING PFT 7_8 inch male 3-pole
HARTING eCatalogue	<a href="https://b2b.harting.com/21043161305">https://b2b.harting.com/21043161305</a>

## Identification

Category	Connectors
Series	Circular connectors 7/8"
Element	Panel feed through
Specification	With conductors for front mounting

## Version

Gender	Male
Shielding	Unshielded
Number of contacts	3
Number of power contacts	2
Number of special contacts	1
Specification of special contacts	PE contact
Locking type	Screw locking

## Technical characteristics

Conductor cross-section	1 mm <sup>2</sup>
Conductor cross-section	AWG 18
Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4.8 kV
Pollution degree	3



**Pushing Performance**  
Since 1945

## Technical characteristics

Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Limiting temperature	$-40 \dots +85 \text{ }^\circ\text{C}$
Ambient temperature	$-40 \dots +85 \text{ }^\circ\text{C}$
Mating cycles	$\geq 100$
Degree of protection acc. to IEC 60529	IP67
Isolation group	I ( $600 \leq \text{CTI}$ )
Conductor length	20 cm

## Material properties

Material (insert)	Thermoplastic polyurethane (TPU)
Material (contacts)	Brass
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Copper-zinc alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
----------	------------------------------------------------------------

## Commercial data

Packaging size	1
----------------	---



Pushing Performance  
Since 1945

Commercial data

Net weight	54 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140382152
eCl@ss	27440103 Sensor-actuator connector chassis (sensor technology actuator)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21043161305](#)