



- Transmission properties in accordance with ISO/IEC 11801: Class E
 - Temperature range: -20° C ... +70° C

All Dimensions in mm Original Size DIN A3		Scale 1.5:1	Free size tol.		Ref.
All rights reserved Department EC PD - RO		Created by TOMUTA	Inspected by AVRAM	Standardisation HOFFMANN	Date 2013-09-30
HARTING Electronics GmbH D-32339 Espelkamp		Title RJ Industrial cable assembly			State Final Release Doc-Key / ECM-Nr. 100081080/UGD/016/B 500000066812
		Type TB	Number 094570XXXXX		Rev. B Page 1/2

1	2	3	4	5	6	7	8	
33	09457011535	8xAWG 26/7, stranded PUR Cat. 6A	2	43	09457011545	8xAWG 26/7, stranded PUR Cat. 6A	20	
32	09457011534		1.5	42	09457011544		15	
31	09457011533		1	41	09457011543		10	
30	09457011532		0.5	40	09457011542		9	
29	09457011576		21	39	09457011541		8	
28	09457011575	20	38	09457011540	7			
27	09457011574	15	37	09457011539	6			
26	09457011573	10	36	09457011538	5			
25	09457011572	9	35	09457011537	4			
24	09457011571	8	34	09457011536	3			
23	09457011570	8xAWG 26/7, stranded PVC Cat. 6A	7					
22	09457011569		6					
21	09457011568		5					
20	09457011567		4					
19	09457011566		3					
18	09457011565		2					
17	09457011564		1.5					
16	09457011563		1					
15	09457011562		0.5					
14	09457002514		8xAWG 26/7, stranded PUR Cat. 7A					20
13	09457002513	15						
12	09457002512	10						
11	09457002511	9						
10	09457002510	8						
9	09457002509	7						
8	09457002508	6						
7	09457002507	5						
6	09457002506	4						
5	09457002505	3						
4	09457002504	2						
3	09457002503	1.5						
2	09457002502	1						
1	09457002501	0.5						
Cont no.	Part no.	Type of cable	Dim a[m]					

 HARTING Electronics GmbH D-32339 Espelkamp	All rights reserved Department EC PD - RO	Created by TOMUTA	Inspected by AVRAM	Standardisation HOFFMANN	Date 2013-09-30	State Final Release
	Title RJ Industrial cable assembly					Doc-Key / ECM-Nr. 100081080/UGD/016/B 50000066812
	Type TB	Number 094570XXXXX			Rev. B	Page 2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09457011576](#)