

A close-up, low-angle shot of a soldier in camouflage gear. The soldier is wearing a headset with a microphone and has various pieces of equipment, including a communication device, attached to their gear. The background is a bright, outdoor setting, possibly a desert or field. The overall tone is professional and military-oriented.

Cables | Adapters | Accessories

For Harsh Environment, Mil/Aero Applications

Amphenol Pcd

Connecting Those Who Protect Us

Amphenol Pcd connects people and technology for those who protect us. We are located in Beverly, Massachusetts and we are dedicated to supplying high quality cables to all branches of the military. Our cables are built for all harsh environments and designed to meet and exceed customer expectations. We have close alliances with other Amphenol divisions, enabling us to competitively offer full turn-key integration of any connector onto a cable assembly. We offer quick-turn prototype services and production programs with short lead-times. Our experienced engineering staff is ready to assist you with any new design effort ranging from connector selection to full cable assembly design. Our facility is ITAR registered and ISO 9001:2008 and AS9100-C certified.

Product Offerings

Amphenol Pcd Cable Solutions specializes in a line of products allowing you to make the connection between virtually any interconnect technologies. Our PRC Kits, Cable Assemblies, Adapter Cables, Pigtails, and Accessory Adapters are examples of accessory products enabling turn-key integration of virtually any connector onto a cable assembly. This includes Amphenol's Mil-Spec connector products D38999s, M55116, M55181, M24308, M26482, Nexus Audio & TAC, and Micro-sub-miniature Circulares, such as Terrapin (SCE) and 2M.

Don't Start Over Adapt

Simply choose the connector you want along with the cable length you need, and we'll make the adapter on demand. Virtually any connector can be used, and although standard options are offered, custom cable adapters can always be made. The possibilities are endless.



Tactical Communications



Rugged Computing



Battlefield Communications



Military Ground Vehicles

PRC Kits & PRC Pigtails

*All PRC Kits available as Pigtails & Custom Assemblies

PRC 117G J3 & J6-PORT



MPC3010



J6 STRAIGHT SIDE

MPC3001



J3 RA FRONT

MPC3002



J3 RA REAR

MPC3000



J3 STRAIGHT SIDE

MPC3011



J6 RA FRONT

PRC 152



MPC3023



152 STRAIGHT UP

MPC3024



152 STRAIGHT DOWN

MPC3021



152 RA FRONT

MPC3022



152 RA REAR

TBD



152 RA REAR Pigtail

PRC Kits

Pigtails & Assemblies

MPC3RRD-XXX-YY-N / MPC3RRD-XXX-YY-N-ZZZ-TW

MPC3 = Prc Product Line

RR = Radio Type
00 = PRC 117G J3-PORT
01 = PRC 117G J6-PORT
02 = PRC 152

D = Connector Direction
0 = Straight Side
1 = Ra Front
2 = Ra Rear
3 = Straight Up
4 = Straight Down

XXX = Cable Jacket Diameter
 Example: 340 = .340"
000 = Double Cable
YY = Strain Relief Material
PL = Standard, Tpu
FR = Flame Retardant, Tpu

N = Standard Shell

ZZZ = Length
 Example: 072 = 72" (6Ft)

T = Cable Type
A = Cable Assembly
P = Pigtail
W = Wiring/Cable/
 Connector

Cable Assemblies

Mil-22992 Class L Heavy Duty Power Cables



Ruggedized Ethernet & USB Cables



Headset & Soldier Accessory Cables



Military Radio Cables



Military Audio Coil Cord Assembly



Harsh Environment Cables



MAC000119-XXX

MAC000117-XXX

MPC3002-000-FR-N-072-A2



Pegasus Size 7 Plug Adapter Cable



M55116 (AP176) to TAC MAP-56-50 Audio Plug Adapter Cable



DSUB RJ45 TO PRC 117G J3 REAR RA

MPC3002-250-PL-N-024-A1

MPC3024-260-PL-N-036-A1

MPC3001-220-PL-N-018-A1



TERRAPIN TO PRC 117G J3 REAR RA



45 CAT5E TO PRC 152 STRAIGHT DOWN



AP-176 TO PRC 117G J3 FRONT RA

MCA103800-XXX

MAC000113-XXX

MAC000114-XXX



2M CONNECTOR BRAIDED CABLE NETWARRIOR ACCESSORY



2M CONNECTOR C1 CABLE NETWARRIOR ACCESSORY



MICRO USB TO 2M CONNECTOR C4R CABLE NETWARRIOR ACCESSORY

Adapter Cables

MAC000101-XXX



2M801-007-16ZNU8-13PA to RJ45 CAT5E plug

MAC000102-XXX



SCE2-B-01K07-14PA to RJ45 CAT5E plug

MAC000103 -XXX



SCE2-B-01K07-14PA to 2M801-007-16ZNU8-13PA

MAC000104-XXX



SCE2-B-01K07-14PN to AJ107

MAC000105 -XXX



M55116 (AP-176) TO USB 2.0 TYPE A plug

MAC000106-XXX



SCE2-B-01K07-14PN to USB 2.0 TYPE A plug

MAC000107-XXX



AJ-107 to USB 2.0 TYPE A plug

MAC000108 -XXX



2M801-007-16MT6-7PA to USB 2.0 TYPE A plug

MAC104900



DSUB 25 Pin to 2M Connector Plug

Accessory Adapters

MAA001001



M55116/8 Receptacle to TAC MAJ-56 Plug

MAA001002



TAC MAP-56 Receptacle to M55116/10 Plug

MAA001003



Power Adapter

Pigtails

MPT000101-XXX



RJ45 CAT5E plug

MPT000102-XXX



SCE2-B-01K07-14PA

MPT000103-XXX



2M801-007-16ZNU8-13PA

MPT000104-XXX



AJ-107

MPT000105-XXX



M55116 (AP-176)

MPT000106-XXX



USB 2.0 TYPE A plug

Adapter Cables & Pigtails Specifications

- Standard cable lengths (Adapter Cables): 8 in, 10 in, 12 in
- Standard cable lengths (Pigtails): 6 in, 12 in, 18 in
- Custom cable lengths are available
- Wiring, labels, & molding markings can be customized upon request
- Meets IPC-WHMA-A-620B
- Quick turnaround times
- XXX = Length in inches (012 = 12 inches)

Ordering Options

Order by Email

Email your engineered drawing and parts list to your local Amphenol Sales Representative or info@amphenolpcd.com

Order by Phone

Call Amphenol Pcd with your cable needs at:
978-624-3400 or 941-773-8560

Amphenol Pcd

Amphenol Pcd

72 Cherry Hill Dr. Beverly, MA. 01915

info@amphenolpcd.com (978) 624.3400

www.amphenolpcd.com

FOLLOW US



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MPC3001](#)