

Product number
10080069-XXXXXXXXLF

PART NUMBER DESCRIPTION:
10080069 - X X X XXXX LF

LF: LEAD FREE (NOTE 10)
CUSTOMER SPECIFIC DASH NUMBER

STYLE:

	END P1 CONNECTOR STYLE	END P2 CONNECTOR STYLE
1:	STRAIGHT	STRAIGHT
2:	STRAIGHT	R/A
3:	R/A	STRAIGHT
4:	R/A	R/A

CODING KEY:

	ORIENTATION P1	ORIENTATION P2
A:	0°	0°
B:	90°	90°
C:	180°	180°
D:	270°	270°
E:	90°	0°
F:	90°	180°
G:	90°	270°
H:	180°	0°
J:	180°	90°
K:	180°	270°

	ORIENTATION P1	ORIENTATION P2
L:	270°	0°
M:	270°	90°
N:	270°	180°
P:	CUSTOMER INSTALLED	CUSTOMER INSTALLED
R:	0°	90°
S:	0°	180°
T:	0°	270°

CABLE DESCRIPTION

	WIRE SIZE	DESCRIPTION	NOTES	STYLE
E:	2 x 6mm ²	STRANDED	HALOGEN FREE	STRAIGHT
F:	10mm ²	STRANDED	HALOGEN FREE	R/A
G:	16mm ²	STRANDED	HALOGEN FREE	STRAIGHT, R/A
H:	25mm ²	STRANDED	HALOGEN FREE	R/A



Copyright FCI.

www.fciconnect.com		surface - <input checked="" type="checkbox"/> ASME Y14.5	tolerance std - <input checked="" type="checkbox"/> ASME Y14.5	projection	MM
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	D. INGRAM	2008-10-09	ANGULAR	size A4	Scale 7:100
Eng	C. GROSS	2008-10-09	LINEAR		
Chr	C. CROSS	2008-10-09	0° ±2°	0.X ±0.X	ECN V09-0194
Appr	C. GROSS	2008-10-09	0.XX ±0.10	0.XXX ±0.XXX	
		Product family	Spec ref		
		PWR TWINBLADE I/O DOUBLE ENDED CABLE ASSEMBLY PART NUMBER SCHEME		dwg no 10080069	Rev. B
catalog no		-		CUSTOMER	sheet 1 of 1

rev	ecn no	dr	date
A	V08-0434	DAI	2008-10-09
B	V09-0194	SM	2009-04-24

REV F - 2006-04-17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10080069-1GM0007LF](#)