

| 1 | | | | | 2 | | | | | 3 | | | | | 4 | | | | | |
|-------|--------------------------|--|--|----|------|------|-------|--------------------------|--|---|----|------|------|-------|--------------------------|--|--|----|------|------|
| COUNT | DESCRIPTION OF REVISIONS | | | BY | CHKD | DATE | COUNT | DESCRIPTION OF REVISIONS | | | BY | CHKD | DATE | COUNT | DESCRIPTION OF REVISIONS | | | BY | CHKD | DATE |
| △ | | | | | | | △ | | | | | | | △ | | | | | | |
| △ | | | | | | | △ | | | | | | | △ | | | | | | |
| △ | | | | | | | △ | | | | | | | △ | | | | | | |

Technical drawing of a connector with dimensions and a watermark 'HRS DRAWING FOR REFERENCE'. The drawing shows a side view of a connector with various dimensions and tolerances. Key dimensions include: 1.6±0.3, 1.3±0.2, 0.5±0.2, 16.5±0.4, 11.5±0.3, 2.4±0.3, 1.8±0.2, 1±0.3, (0.3), (0.1), 4.6±0.3, (0.8), 2.4±0.3, 0.8±0.3, 1.5±0.3, 3±0.3, 3±0.3, 1.4±0.2, (6.5), 4.9±0.3. A note indicates 'SIDE CUT OPTIONAL. (SIZE AND STYLE ALSO OPTIONAL.) THE DIMENSION IN PARENTHESES ARE FOR REFERENCE.' A callout '1' points to a specific feature.

| NO. | MATERIAL | FINISH, REMARKS | NO. | MATERIAL | FINISH, REMARKS |
|-----|-----------------|--|-----|----------|-----------------|
| 1 | PHOSPHOR BRONZE | CONTACT AREA: GOLD PLATED 0.2μm UNDER PLATING: NICKEL 0.5μm | | | |

| CODE NO. (OLD) | DRAWN | DESIGNED | CHECKED | APPROVED | RELEASED |
|----------------|----------|-------------|----------|-------------|----------|
| CL | S.SUZUKI | H. Nakamura | H. Okawa | T. Takemura | |
| | 03.05.28 | 03.05.28 | 03.05.28 | 03.05.29 | |

| DRAWING NO. | PART NO. |
|-------------|---------------|
| EDC4-017874 | HIF3-2630SCFC |

| SCALE | UNITS | CODE NO. |
|--------|-------|--------------|
| 10 : 1 | mm | CL613-0001-9 |

HRS HIROSE ELECTRIC CO., LTD.

TO PCK

FORM NO. 225

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[HIF3-2630SCFC](#)