

HAND TOOL TOOLING SHEET

Revised 07/12/10 REV 15

PRODUCT FAMILY	WIRE SIZE	CONTACT	REDUCING BUSHING	HAND TOOL			INSTRUCTION SHEET TOOLS	INSTRUCTION SHEET CONNECTORS						
				TOOL	LOCATOR	CAVITY								
Pin and Socket 10 Amp	14-16 AWG	1203G1 (PIN)	N/A	1309G1	N/A	C	1S6373	N/A						
		1202G1 (Soc)												
Pin and Socket 30 Amp	10-14 AWG	1230G1 Pin	N/A	1396G1	N/A	N/A	1S6345	1S6344						
		1232G1 Socket												
		1231G1 Pin												
		1233G1 Socket												
	10 AWG Superflex	1226G1 Pin												
		1228G1 Socket												
PP15/45	16-20 AWG	1332	N/A	1309G2	N/A	N/A	1S6373	1S1072						
	12-16 AWG	1331												
	16-20 AWG	262G1-LPBK												
	12-16 AWG	261G1-LPBK												
	10-12 AWG	261G2-LPBK												
	14-16 AWG													
	10-12 AWG													
	14 AWG													
	10-12 AWG	261G2-LPBKSP												
	14 AWG													
	12-16 AWG													
	10-14 AWG	269G1-LPBK												
	16-20 AWG	269G2-LPBK												
	6mm, #10-14 AWG	200G1L-LPBK												
	#16-20 AWG	200G2L-LPBK												
	#10-14 AWG	201G1H-LPBK												
	6mm, #10-14 AWG	1830G1-LPBK												
	PP75/SB50 W/O BUSHINGS	#6 AWG		5900					N/A	1309G4	N/A	Lrg	1S6373	1S1072/1S1030A
				1307										
#8 AWG		5952												
#10-12 AWG		5915												
#10 AWG		5914 (Thin Wall)												
#6 AWG		1C0608P32 (Low det Ni Plate)												
#10-12 AWG		1C0608P33 (Low det Ni Plate)												
#6 AWG		1C0608P36 (Low Det)												
PP75/SB50 With Bushings	#8 AWG	5900	N/A	1309G4	N/A	Lrg	1S6373	1S1072/1S1030A						
	#10-12 AWG								5912					
	#14-16 AWG								5910					
SBS 50	16mm	1339G2	N/A	1309G4	N/A	N/A	1S6373	1S6417						
	#10/12	1339G3												
	#8	1339G5												
SBS 50 With Bushings	#8 AWG	1339G2	N/A	1309G4	N/A	N/A	1S6373	1S6417						
	#10/12AWG								5912					
	#14/16AWG								5910					
SBO 60/ SBE 80	16mm	1339G1	N/A	1309G4	N/A	N/A	1S6373	1S6330/1S6331						
	25mm	1339G4												

HAND TOOL TOOLING SHEET

Revised 07/12/10 REV 15

PRODUCT FAMILY	WIRE SIZE	CONTACT	REDUCING BUSHING	HAND TOOL			INSTRUCTION SHEET TOOLS	INSTRUCTION SHEET CONNECTORS
				TOOL	LOCATOR	CAVITY		
EBC Auxiliary Contacts	2.5mm ²	E80-30	N/A	1309G4	N/A	Sml	1S6373	1S6449/1S6450
		E80-31						
	14/18 AWG **	320-22						
		320-23						
		320-24						
	320-25							
**Two 18 AWG may be used in one barrel								
Power Mod	#12-24 AWG	All contacts	N/A	TM0001	TL0004	N/A	N/A	1S6420
Power Drawer	#12-24 AWG	All Crimp contacts	N/A	TM0001	TL0003	N/A	N/A	1S6416

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anderson Power Products:](#)

[TL0004](#)