

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008580111](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK Trifurcon Crimp Terminal 6438, 18-20 AWG, Bag, Phosphor Bronze Selective Gold (Au)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001-001 \(PDF\)](#)
[Product Specification PS-40-02-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [6838](#)
 Application Power, Wire-to-Board
 Crimp Quality Equipment Yes
 Overview [KK Interconnect Solutions](#)
 Packaging Alternative [08580110 \(Reel\)](#)
 Product Name KK 396, Trifurcon
 UPC 800754226936

Physical

Gender Female
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Nickel
 Net Weight 0.197/g
 Packaging Type Bag
 Plating min - Mating 0.762µm
 Plating min - Termination 1.270µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.79mm max.
 Wire Size AWG 18, 20
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 6838-A(P561)L

Reference - Drawing Numbers

Packaging Specification PK-2759-001-001
 Product Specification PS-40-02-001
 Sales Drawing SD-6838-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[6838 Series](#)

Use With

[KK Crimp Terminal Housing 6442](#) , [41695](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 18-24 AWG	11030016

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[08-58-0111](#)