

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039532235](#)
Status: **Active**
Overview: FFC-FPC (Through-Hole)
Description: 1.25mm Pitch Easy-On FFC/FPC Connector, Through-Hole, Vertical, ZIF, 23 Circuits

Documents:

| | |
|--------------------------------|--|
| 3D Model | Product Specification PS-5597-004-001 (PDF) |
| Drawing (PDF) | Packaging Specification SPK-5597-001-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

UL E29179

General

| | |
|----------------|--|
| Product Family | FFC/FPC Connectors |
| Series | 5597 |
| Overview | FFC-FPC (Through-Hole) |
| Product Name | Easy-On |
| UPC | 822348190188 |

Physical

| | |
|--------------------------------|-----------------|
| Actuator Type | Slider |
| Circuits (Loaded) | 23 |
| Circuits (maximum) | 23 |
| Color - Resin | Natural |
| Contact Position | N/A |
| Durability (mating cycles max) | 30 |
| Flammability | 94V-0 |
| Mated Height | 7.50mm |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin-Bismuth |
| Material - Plating Termination | Tin-Bismuth |
| Material - Resin | Polyester |
| Net Weight | 2002.060/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 3.50mm |
| PCB Locator | No |
| PCB Mounting | Through Hole |
| PCB Retention | None |
| Packaging Type | Tray |
| Pitch - Mating Interface | 1.25mm |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Polarized to PCB | No |
| Stackable | No |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -20° to +80°C |
| Wire/Cable Type | FFC/FPC |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 200V |

Material Info

Engineering Number 5597-23CPB7F

Reference - Drawing Numbers



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5597 Series](#)

Packaging Specification
Product Specification
Sales Drawing

SPK-5597-001-001
PS-5597-004-001
SD-5597-007-001, SD-5597-007-002

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39-53-2235](#)