

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0134223011](#)  
**Status:** **Active**  
**Overview:** [Asset Tracking Solutions](#)  
**Description:** Alien Enterprise 4-port Fixed RFID Reader Kit, 916-928 MHz, for Uruguay and Peru

**Documents:**

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Kit components**

Kit Components Reader, PoE Injector, Power Cable for PoE Injector/Reader, Two Ethernet Cables, USB Cable (Type B to A), I/O Mating Connector)

**General**

Product Family RFID Products  
 Series [13422](#)  
 Component Type Fixed RFID Reader  
 Kit Option Reader Kit  
 LAN Protocols TCP/IP,NTP,DNS,DHCP,SNMP  
 Market Peru, Uruguay  
 More Detailed Tech Information For detailed product and compliance certification information, please <a href="https://www.alientechnology.com/download/alr-f800-documents/?wpdmdl=7608&ind=QUxSLUY4MDAgKDIwMTktMDEtMjM0LmR2Zy" >https://www.alientechnology.com/download/alr-f800-documents/?wpdmdl=7608&ind=QUxSLUY4MDAgKDIwMTktMDEtMjM0LmR2Zy</a>  
 Overview [Alien Datasheet](#)  
 Product Name [Asset Tracking Solutions](#)  
 RFID Standard Alien  
 Reader Protocols EPC C1 Gen 2,ISO 18000-6c  
 Type ARP,LLRP  
 UPC Enterprise  
 193264422135

**Physical**

Additional Readers Supported None  
 Antennas Up to 4 Supported  
 Communications LAN TCP/IP (RJ-45), RS-232 (DB-9 F), USB Console, USB Host  
 Dimensions 202.00 x 191.00 x 28.00mm  
 General Purpose I/O 4 in / 8 out (Isolated)  
 Memory 512 MB RAM,2 GB Flash  
 Operating System Linux  
 Packaging Type Carton  
 Software SDK Java,.NET,Ruby APIs  
 Temperature Range - Operating -20° to +50°C

**Electrical**

Frequency 916-928 MHz  
 Max Conductive RF Power (dBm) 31.6  
 Power Source PoE,AC/DC Power Converter

**Material Info**

Engineering Number F800-URY-RDR-KIT



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

**Not Reviewed**

**ELV**

**Not Reviewed**

**RoHS Phthalates**

**Not Reviewed**

**Search Parts in this Series**

[13422 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[13422-3011](#)