

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0150200208**  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 51.00mm Cable Length, Gold (Au) Plating, 20 Circuits

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Product Specification PS-15020-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<u>15020</u>
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<u>FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</u>
Product Name	Premo-Flex FFC Jumper
UPC	884982176706

**Physical**

Cable Length	51.00mm
Circuits (Loaded)	20
Contact Layout Type	D (opposite side)
Material - Plating Mating	Gold
Net Weight	0.354/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-15020-001-001
Sales Drawing	SD-15020-001-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

15020 Series

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[5034802000](#) , [5051102091](#) , [527452097](#) ,  
[527462071](#) , [5019512010](#) , [5019512030](#) ,  
[5019512050](#) , [525592052](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15020-0208](#)