

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0152670722](#)
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 30.00mm Cable Length, Tin (Sn) Plating, 5 Circuits

Documents:

Drawing (PDF)	Datasheet (PDF)
Product Specification PS-15267-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	15267
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	884982449664

Physical

Cable Length	30.00mm
Circuits (Loaded)	5
Contact Layout Type	D (opposite side)
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-15267-001-001
Sales Drawing	SD-15267-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
ECHA_01_2020 (16
January 2020)
Sodium perborate;
perboric acid, sodium
salt
Methylhexahydrophthalic
anhydride
4-(1,1,3,3-
tetramethylbutyl)phenol,
ethoxylated
Trixylyl phosphate
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
pentacosafuorotridecanoic
acid
sodium
peroxometaborate
henicosafuoroundecanoic
acid
1,2-diethoxyethane
methoxyacetic acid
heptacosafuorotetradecanoic
acid
tricosafuorododecanoic
acid
furan
Imidazolidine-2-thione
Dinoseb
Acetamide, N-methyl-
diethyl sulphate
Diboron-trioxide
4,4'-
bis(dimethylamino)-4"-
(methylamino)trityl
1,2-bis(2-
methoxyethoxy)ethane

China RoHS

N,N,N',N'-
tetramethyl-4,4'-
methyldianiline
4,4'-
bis(dimethylamino)benzophenone
formamide

4,4'-
diaminodiphenylmethane
1-bromopropane

Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[15267](#) Series

Mates With

Easy-On FFC/FPC Connector:

[522070533](#) , [522710579](#) , [526100533](#)

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15267-0722](#)