

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190710334](#)  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** InsulKrimp Ring Tongue Terminal for 8 AWG Wire

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-19902-011-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-19902-009-001 (PDF)</a>	

**Agency Certification**

CSA	LR18689
UL	E32244

**General**

Product Family	Ring and Spade Terminals
Series	<a href="#">19071</a>
Crimp Quality Equipment	Yes
Overview	<a href="#">Solderless Terminals</a>
Product Name	InsulKrimp
Type	Ring
UPC	800753073012

**Physical**


Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	5.006/g
Packaging Type	Bag
Stud Size	1/2" (M12)
Wire Insulation Diameter	6.70mm max.
Wire Size AWG	8

**Material Info**

Engineering Number	D-652-12X
--------------------	-----------

**Reference - Drawing Numbers**

Product Specification	PS-19902-009-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19071-002-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19071 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Manual Putt Pump Hydraulic System, Die set required	<a href="#">192860117</a>
Die Set (large) for the HHLS Hydraulic Crimper	<a href="#">192890001</a>
Hydraulic Dieless Crimping Tool	<a href="#">638161700</a>
PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	<a href="#">640013900</a>
Crimp Tool Kit for 8 AWG Insulated Ring Terminals	<a href="#">640017670</a>

This document was generated on 01/17/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19071-0334](#)