

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191640034**
Status: **Active**
Overview: Perma-Seal Terminals
Description: Perma-Seal Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 10 (M5)

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19164</u>
Crimp Quality Equipment	Yes
Overview	<u>Perma-Seal Terminals</u>
Product Name	Perma-Seal
Type	Ring
UPC	800753113220

Physical

Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	1.161/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Insulation Diameter	5.97mm
Wire Size AWG	14, 16
Wire Size mm ²	1.23-1.94

Material Info

Engineering Number	SB-237-10
--------------------	-----------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-026-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade [640017400](#)

Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)

Power Crimp Tool [640057400](#)

Head for Terminals 10-22 AWG Wire

ServiceGrade Hand [640160041](#)

Crimp Tool for Field Repair only, for production use our PremiumGrade Tool

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19164-0034](#)