

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190820013**
Status: **Active**
Overview: Battery Cable Lugs
Description: Compression Style Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Plated, Mylar Tape Carrier

Documents:

[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Ring and Spade Terminals
Series 19082
Comments Heavy Duty
Crimp Quality Equipment Yes
Overview Battery Cable Lugs
Product Name Battery Cable Lug
Type Ring
UPC 800753084711

Physical


Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Net Weight 5.271/g
Packaging Type Adhesive Tape on Reel
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 1/4" (M6)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter N/A
Wire Size AWG 8
Wire Size mm² 6.60-10.50

Material Info

Engineering Number BCL-814-PLT

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-015-001
Sales Drawing SD-19221-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19082 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

ATP Perishable [190270123](#)

Tool Kit used in ATP presses that process product on tape

Crimp Dies for 8 [190472090](#)

AWG BCL's Mylar Tape, use with the 640162000 Tape Crimp Module and 638017600 TM-4000 Crimp Press

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19082-0013](#)