

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191930209**
Status: **Active**
Overview: VersaKrimp Terminals and Splices
Description: VersaKrimp Ring Tongue Terminal for 6 AWG Wire

Documents:

Drawing (PDF) Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF) RoHS Certificate of Compliance (PDF)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19193
 Crimp Quality Equipment Yes
 Overview VersaKrimp Terminals and Splices
 Product Name VersaKrimp
 Type Ring
 UPC 800755050592

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 6.270/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Stud Size 10 (M5)
 Termination Interface: Style Crimp or Compression
 Wire Size AWG 6

Material Info

Engineering Number E-357-10

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19193-015-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19193 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|---|------------------|
| Manual Putt Pump Hydraulic System, Die set required | <u>192860117</u> |
| Die Set (large) for the HHLS Hydraulic Crimper | <u>192900004</u> |
| Hydraulic Dieless Crimping Tool | <u>638161700</u> |
| PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals | <u>640013900</u> |
| Square "DIN" style dies for 6 AWG | <u>640037770</u> |

Crimp Head for the 640074300
AT-200 Pneumatic
Hand Tool

This document was generated on 09/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19193-0209](#)