

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192050009**
Status: **Active**
Overview: [Splices](#)
Description: VersaKrimp Parallel Splice for 1/0 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family [Splices](#)
 Series [19205](#)
 Crimp Quality Equipment Yes
 Overview [Splices](#)
 Product Name Parallel, VersaKrimp
 UPC 800755060881

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 13.336/g
 Packaging Type Bag
 Wire Size AWG 1/0

Material Info

Engineering Number H-384

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19205-007-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19205 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192900011
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
Hydraulic Dieless Crimping Tool	638161700
Square "Din" Style Die Set for BCL	640038070

and VersaKrimp
Un-insulated Ring
Tongue Terminals
and Splices, 1/0 and
2/0 AWG

This document was generated on 10/01/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19205-0009](#)