

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0387112203](#)
Status: **Active**
Overview: Beau Barrier Strips
Description: 9.53mm Pitch Beau PCB Terminal Strip, Low Profile, Wire Wrap Terminal, 3 Circuits

Documents:

[3D Model](#) [Product Specification PS-38710-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family Terminal Blocks
Series [38711](#)
Application N/A
Component Type One Piece
Overview [Beau Barrier Strips](#)
Product Name Fixed Mount Barrier
Type Barrier Strip
UPC 800756294131

Physical

Circuits (Loaded) 3
Circuits (maximum) 3
Color - Resin Black
Entry Angle Horizontal
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester
Number of Rows 1
Orientation Horizontal
PC Tail Length 11.90mm
PCB Retention Yes
Panel Mount No
Pitch - Mating Interface 9.53mm
Pitch - Termination Interface 9.53mm
Polarized to Mating Part No
Shrouded Dual-Barrier
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +130°C
Termination Interface: Style Screw or Lug
Wire Size AWG 14, 16, 18, 20, 22
Wire Size mm² 0.50-1.50

Electrical

Current - Maximum per Contact 15.0A
Voltage - Maximum 300V

Solder Process Data


Lead-freeProcess Capability WAVE

Material Info

Engineering Number 71703

Reference - Drawing Numbers

Product Specification PS-38710-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[38711 Series](#)

This document was generated on 08/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38711-2203](#)