

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0355240929](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: [VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, with Mounting Ears, 9 Circuits, Natural, Glow-Wire Capable](#)

Documents:

3D Model	Application Specification 351500000ASKOR-000 (PDF)
3D Model (PDF)	Packaging Specification PK-35524-001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-35524-001-001 (PDF)	Brochure (PDF)
Application Specification 351500000ASENG-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	35524
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	756054284483

Physical

Breakaway	No
Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	11.989/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	6.20mm, 7.30mm
Pitch - Termination Interface	6.20mm, 7.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Material Info

Reference - Drawing Numbers

Application Specification	351500000AS_ENG-000 , 351500000AS_KOR-000
Packaging Specification	PK-35524-001-001
Product Specification	PS-35524-001-001
Sales Drawing	SD-35524-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[35524 Series](#)

Mates With

VersaBlade 2 Circuit Plug Housing
[351510210](#) , [351510214](#) , [351510219](#)
 , [351512219](#) , [351513219](#) , [351514219](#)

VersaBlade 3 Circuit Plug Housing
[351510310](#) , [351510314](#) , [351510319](#)
 , [351514319](#)
VersaBlade 4 Circuit
Plug Housing [351510410](#) , [351510414](#) ,
[351510419](#) , [351514419](#)

Use With

VersaBlade Crimp Terminals [35745](#) (ckt
1, 2, 3), [35746](#) (ckt 4, 6, 7), [35747](#) (ckt
5, 8, 9) . VersaBlade TPA (for 2 and 4
ckt housing) [351500290](#) , [351500292](#) ,
[351500293](#) , [351500294](#) . VersaBlade TPA
(for 3 ckt housing) [351500390](#) , [351500392](#) ,
[351500393](#) , [351500394](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35524-0929](#)