

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0387207505](#)  
**Status:** **Active**  
**Overview:** Beau Barrier Strips  
**Description:** 9.53mm Pitch Beau PCB Terminal Strip, without Mounting Ends, 5 Circuits, with Screw Clamp Washer

**Documents:**

[3D Model](#) [Product Specification PS-38710-001-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family Terminal Blocks  
Series [38720](#)  
Application N/A  
Component Type One Piece  
Overview Beau Barrier Strips  
Product Name Fixed Mount Barrier  
Type Barrier Strip  
UPC 800756177250

**Physical**

Circuits (Loaded) 5  
Circuits (maximum) 5  
Color - Resin Black  
Entry Angle Horizontal  
Lock to Mating Part None  
Material - Metal Brass  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Material - Resin Polyester  
Net Weight 20.910/g  
Number of Rows 1  
Orientation Horizontal  
PC Tail Length 4.80mm  
PCB Retention None  
PCB Thickness - Recommended 3.18mm  
Panel Mount No  
Pitch - Mating Interface 9.53mm  
Pitch - Termination Interface 9.53mm  
Plating min - Mating 3.810µm  
Plating min - Termination 3.810µm  
Polarized to Mating Part No  
Shrouded Dual-Barrier  
Stackable No  
Surface Mount Compatible (SMC) No  
Temperature Range - Operating -40° to +130°C  
Wire Size AWG 12, 14, 16, 18, 20, 22  
Wire Size mm² 0.50-2.50


**Electrical**

Current - Maximum per Contact 25.0A  
Voltage - Maximum 300V

**Solder Process Data**

Lead-freeProcess Capability WAVE

**Material Info**



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[38720 Series](#)

**Mates With**

N/A

Engineering Number

72505-C-50

**Reference - Drawing Numbers**

Product Specification

PS-38710-001-001

Sales Drawing

SD-38720-002

This document was generated on 07/26/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38720-7505](#)