

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0398801204](#)
Status: **Active**
Overview: Eurostyle Terminal Blocks
Description: 5.08mm Pitch Horizontal Fixed Mount PCB Terminal Block, 4 Circuits

Documents:

| | |
|--------------------------------|--|
| 3D Model | Drawing (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR25562 |
| UL | E48521 |

General

| | |
|----------------|---|
| Product Family | Terminal Blocks |
| Series | 39880 |
| Application | N/A |
| Component Type | One Piece |
| Overview | Eurostyle Terminal Blocks |
| Product Name | Eurostyle Fixed Mount |
| Type | Euro Block |
| UPC | 800756723792 |

Physical

| | |
|--------------------------------|--|
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Entry Angle | 90° Angle |
| Flammability | 94V-0 |
| Lock to Mating Part | None |
| Number of Rows | 1 |
| Orientation | Horizontal |
| PC Tail Length | 3.60mm |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.57mm |
| Panel Mount | No |
| Pitch - Mating Interface | 5.08mm |
| Pitch - Termination Interface | 5.08mm |
| Polarized to Mating Part | Yes |
| Shrouded | Fully |
| Stackable | No |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | 12, 14, 16, 18, 20, 22, 24, 26, 28, 30 |

Electrical


| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 17.5A |
| Voltage - Maximum | 300V |

Material Info

| | |
|--------------------|----------------|
| Engineering Number | MX-MSM04095-0N |
|--------------------|----------------|

Reference - Drawing Numbers

| | |
|---------------|--------------|
| Sales Drawing | SD-39880-011 |
|---------------|--------------|



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[39880 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39880-1204](#)