

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0528921133**
Status: **Active**
Overview: Easy-On FFC FPC Connectors
Description: 0.50mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, Cable Retention Guide, 11 Circuits

Documents:

[3D Model](#) [Product Specification PS-52892-040-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification SPK-52892-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
Series [52892](#)
Comments Hinge, Cable Guide
Overview [Easy-On FFC FPC Connectors](#)
Product Name Easy-On
UPC 887191273433

Physical

Actuator Type Front Flip
Circuits (Loaded) 11
Color - Resin Natural
Contact Position Bottom
Durability (mating cycles max) 20
Mated Height 2.00mm
Material - Metal Phosphor Bronze
Material - Plating Mating Tin-Silver-Bismuth
Material - Plating Termination Tin-Silver-Bismuth
Material - Resin Nylon
Net Weight 146.524/mg
Number of Rows 1
Orientation Right Angle
PC Tail Length 2.00mm
PCB Locator No
PCB Mounting Surface Mount
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.50mm
Pitch - Termination Interface 0.50mm
Polarized to PCB No
Stackable No
Surface Mount Compatible (SMC) N/A
Temperature Range - Operating -40° to +85°C
Wire/Cable Type FFC/FPC


Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 50V

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-52892-001-001
Product Specification PS-52892-040-001
Sales Drawing SD-52892-044, SD-52892-045



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[52892 Series](#)

This document was generated on 12/01/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52892-1133](#)