

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0528072210](#)  
**Status:** **Active**  
**Overview:**  
**Description:** 1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 22 Circuits

**Agency Certification**

UL E29179

**General**

Product Family FFC/FPC Connectors  
 Series [52807](#)  
 Overview [easyon\\_ffc\\_fpc\\_connectors](#)  
 Product Name Easy-On  
 UPC 800754313971

**Physical**

Actuator Type Non-ZIF  
 Circuits (Loaded) 22  
 Color - Resin Natural  
 Contact Position Top  
 Flammability 94V-0  
 Mated Height 3.60mm  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin High Temperature Thermoplastic  
 Net Weight 674.101/mg  
 Number of Rows 1  
 Orientation Right Angle  
 PC Tail Length 3.20mm  
 PCB Mounting Through Hole - Kinked Pin  
 PCB Retention None  
 Packaging Type Tray  
 Pitch - Mating Interface 1.00mm  
 Pitch - Termination Interface 1.00mm  
 Plating min - Mating 0.914µm  
 Plating min - Termination 0.914µm  
 Polarized to PCB Yes  
 Stackable No  
 Surface Mount Compatible (SMC) No  
 Temperature Range - Operating -20° to +80°C  
 Wire/Cable Type FFC/FPC

**Electrical**

Current - Maximum per Contact 0.2A, 0.4A, 0.5A  
 Voltage - Maximum 50V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification SPK-52807-001-001  
 Product Specification PS-52807-003-001  
 Sales Drawing 528071000-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2021)4569-DC (8  
 July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[52807](#) Series

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52807-2210](#)