

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0622018668](#)
Status: **Active**
Overview:
Description: Press-In Tool for Power Module Assembly

General

Product Family	Application Tooling
Series	207123
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	application_tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982116269
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents [ATS-622018668, TM-622018799](#)

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207123](#) Series

Use With

[78215](#) Impact Power Module Assembly,
Right Angle, 5-Pair Assemblies

Application Tooling | **FAQ**

Description

Product #

Impact 5 Pair, Right- [782151011](#)

Angle Power Header,
Press-Fit, Blade
A1 & A2, B1 & B2
Length 6.90mm,
LCP, Glass Filled,
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- [782151022](#)

Angle Power Header,
Press-Fit, Blade
A1 & A2, B1 & B2
Length 5.70mm,
LCP, Glass Filled,
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- [782151033](#)

Angle Power Header,
Press-Fit, Blade
A1 & A2 Length
5.70mm, B1 & B2
Length 6.90mm,
LCP, Glass Filled,
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- 782151044
Angle Power Header,
Press-Fit, Blade
A1 & A2 Length
6.90mm, B1 & B2
Length 5.70mm,
LCP, Glass Filled,
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, 782491001
Right-Angle Power
Receptacle, Press-
Fit, LCP, Glass Filled
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- 783511001
Angle Power Header,
Left Hold-Down,
Module 1: P1 &
P2, Blade Length
6.90mm; Press-Fit,
LCP, Glass Filled
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- 783511004
Angle Power Header,
Left Hold-Down,
Module 1: P1 &
P2, Blade Length
5.60mm & 6.90mm;
Press-Fit, LCP,
Glass Filled UL94-
V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- 783511011
Angle Power Header,
2 Modules with Left
Hold-Down, Module
1: P1 & P2, Blade
Length 6.90mm;
Module 2: P1 &
P2, Blade Length
6.90mm; Press-Fit,
LCP, Glass Filled
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- 783511021
Angle Power Header,
2 Modules with Left
Hold-Down, Module
1: Blade A1 & A2,
B1 & B2 Length
5.70mm; Module
2: Blade A1 & A2,
B1 & B2 Length
6.90mm; Press-Fit,
LCP, Glass Filled
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair Right- [783511044](#)
Angle Power Header,
2 Modules with
Left Hold-Down,
Module 1: Blade P1
& P2, Length 5.70
& 6.90mm; Module
2: Blade P1 & P2
Length 5.70mm &
6.90mm Press-Fit,
LCP, Glass Filled
UL94-V0, Black,
Lead-Free

Impact 5 Pair, Right- [783512001](#)
Angle Power Header,
Right Hold-Down,
Module 1: P1 &
P2, Blade Length
6.90mm; Press-Fit,
LCP, Glass Filled
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- [783512004](#)
Angle Power Header,
Right Hold-Down,
Module 1: P1 &
P2, Blade Length
5.70mm & 6.90mm;
Press-Fit, LCP,
Glass Filled UL94-
V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair, Right- [783512011](#)
Angle Power Header,
2 Modules with Right
Hold-Down, Module
1: P1 & P2, Blade
Length 6.90mm;
Module 2: P1 &
P2, Blade Length
6.90mm; Press-Fit,
LCP, Glass Filled
UL94-V0, Black, Tray
Packaging, Lead-
Free

Impact 5 Pair Right- [783512042](#)
Angle Power Header,
2 Modules with
Left Hold-Down,
Module 1: Blade P1
& P2, Length 5.70
& 5.70mm; Module
2: Blade P1 & P2
Length 5.70mm &
6.90mm Press-Fit,
LCP, Glass Filled
UL94-V0, Black,
Lead-Free

Impact 5 Pair, Right- [784532501](#)
Angle Power Header,
Integrated Guide
Module w/ESD clip,
Module 1: Blade

A1 & A2, B1 & B2
Length 6.90mm;
Press-Fit, LCP,
Glass Filled UL94-
V0, Black, Tray
Packaging, Lead-
Free, key orientation
E

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8668](#)