

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0622018988](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Impel Backplane Assembly Press-In Tool


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impel
Tool Type	Press-Fit Insertion Tool
UPC	887191587448
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents [ATS-622018988](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207123 Series](#)

Use With

[171745](#) Impel Backplane Assembly, (2-Pair by 12 Column Assemblies)

Application Tooling | [FAQ](#)

Description	Product #
Impel 90 Ohm, 2 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Open Endwalls, 12 Columns, 48 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.36mm	1717451207
Impel 90 Ohm, 2 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Open Endwalls, 12 Columns, 48 Circuits, Pin Length 5.50mm,	1717451208

Plated Through Hole
Dimension 0.36mm
Impel 90 Ohm 2 Pair 1717455208
Vertical Backplane
Header, 1.90mm
Pitch, Right Guided,
12 Columns, 48
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.36mm

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8988](#)