

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0622018782](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Daughter Card Module Installation Press-In Tool


**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207123</a>
Function	Insertion
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982282131
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**  
Application Tooling Documents [ATS-622018782](#)



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207123 Series](#)

**Use With**

Impact Daughtercard Signal Module Assembly (5-Pair by 14 Column Assemblies) [76060](#)

**Application Tooling** | **FAQ**

**Description** | **Product #**

Impact 100 Ohm [760601014](#)

5 Pair Right-Angle Daughtercard Receptacle, Unguided, 14 Columns, 210 Circuits, Plated Through Hole Dimension 0.46mm, Lead Free

Impact 100 Ohm [760601024](#)

5 Pair Right-Angle Daughtercard Receptacle, Unguided, 14 Columns, 210 Circuits, Plated

Through Hole  
Dimension 0.39mm,  
Lead-Free  
Impact 100 Ohm 760603014  
5 Pair Right-Angle  
Daughtercard  
Receptacle, Left  
Guided, 14 Columns,  
210 Circuits, Plated  
Through Hole  
Dimension 0.46mm,  
Lead Free  
Impact 100 Ohm 760603024  
5 Pair Right-Angle  
Daughtercard  
Receptacle, Left  
Guided, 14 Columns,  
210 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Lead Free  
Impact 100 Ohm 760605014  
5 Pair Right-Angle  
Daughtercard  
Receptacle, Right  
Guided, 14 Columns,  
210 Circuits, Plated  
Through Hole  
Dimension 0.46mm,  
Lead Free  
Impact 100 Ohm 760605024  
5 Pair Right-Angle  
Daughtercard  
Receptacle, Right  
Guided, 14 Columns,  
210 Circuits, Plated  
Through Hole  
Dimension 0.39mm,  
Lead Free

This document was generated on 02/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8782](#)