

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638017200](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207125
Application Tooling Video	www.youtube.com/watch?v=1Gj31xD5L_c , www.youtube.com/watch?v=lj0kZ20_wTo , www.youtube.com/watch?v=0avd9Rlph58 , www.youtube.com/watch?v=LjjqR9hEuNk
Comments	2.0 Ton Press, 30mm press stroke
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	TM-3000
Tool Type	Electric Press
UPC	822350060769
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number TM3000

Reference - Drawing Numbers

Application Tooling Documents
 ATS-640162595-001, TM-638000029-001,
 TM-638000029SP-001, TM-638017299-001,
 TM-638017299CH-001, TM-638017299SP-001,
 TM-640160065-001, TM-640160065CN-001,
 TM-640162000-001, TM-640162000SP-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

China RoHS

Search Parts in this Series

[207125 Series](#)

Use With

Molex FineAdjust and Mini-Mac Applicators plus the Molex Tape Crimp Module [640162000](#) and most industry standard applicators.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63801-7200](#)