

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638113800](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: PremiumGrade Hand Crimp Tool for 10.00mm Mini-Fit Sr. Male and Female Terminals, 14-16 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	Prototype and field repair. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054660201
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.


Physical

Net Weight 428.885/zg

Material Info

Reference - Drawing Numbers

Application Tooling Documents
ATS-6381138HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129](#) Series

Use With

Loose Piece Terminals

Application Tooling

Description

FAQ

Product #

Mini-Fit Sr. Crimp Terminal, Female, 14-16 AWG, Gold (Au) [428150042](#)

Mini-Fit Sr. Crimp Terminal, Female, 14-16 AWG, Silver (Ag) [428150144](#)

Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Gold (Au) [428170042](#)

Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Tin (Sn) [428170141](#)

Mini-Fit Sr. Crimp Terminal, Male, [428170142](#)

14-16 AWG, Gold (Au) Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Silver (Ag)	<u>428171044</u>
Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Silver (Ag)	<u>428171144</u>

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-3800](#)