

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638950400](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Mini-Mac Applicator for MX150L Terminals, for 10-12 AWG Wire with Insulation  
 Diameter 3.90-4.85mm

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207127</a>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	Mini-Mac
Tool Type	Applicator
UPC	883906513146
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 4890.929/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
 ATS-638950400-001, TM-638800000-001,  
 TM-638800000SP-001

*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207127](#) Series

**Use With**

Molex TM-3000: [638017200](#) , [638017300](#)  
 , Molex TM-4000: [638017600](#) , Molex  
 TM-2000: [638008300](#) , [638008400](#) , and  
 Most Industry Standard Presses or Wire  
 Process Machines

**Application Tooling**

**FAQ**

**Description**

**Product #**

MX150L Male [194310001](#)

Terminal for 10-12

AWG Wire, Metal

Strip Carrier

MX150L Female [194340001](#)

Terminal for 10-12

AWG Wire, Metal

Strip Carrier

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63895-0400](#)