

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0639019600](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** FineAdjust Applicator for 2.00mm Pitch Female Terminals, 22-28 AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207127</a>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982219595
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 4998.727/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
 ATS-639019600-001, TM-638000029-001,  
 TM-638000029CN-001, TM-638000029DE-001,  
 TM-638000029FR-001, TM-638000029IT-001,  
 TM-638000029JP-001, TM-638000029KR-001,  
 TM-638000029MY-001, TM-638000029PL-001,  
 TM-638000029RU-001, TM-638000029SK-001,  
 TM-638000029SP-001, TM-638000029TH-001,  
 TM-638000029TW-001, TM-638000029VN-001,  
 TM-638004900-001, TM-638004900CN-001,  
 TM-638004900SP-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207127](#) Series

**Use With**

Molex TM-3000: [638017200](#) , [638017300](#)  
 , Molex TM-4000: [638017600](#) , Molex  
 TM-2000: [638008300](#) , [638008400](#) , and  
 Most Industry Standard Presses or Wire  
 Process Machines

**Application Tooling**

**FAQ**

**Description**

**Product #**

2.00mm Pitch Crimp [561349000](#)

Terminal, Female,  
 22-28 AWG, Copper  
 Alloy, Reel

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63901-9600](#)