

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0640080770](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Square DIN style die sets used with Metric 70mm<sup>2</sup> (2/0 AWG) compression lugs

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	See Tooling Specification (PDF) Above. The Square "DIN" style die sets are used with two machines and each machine requires an adapter for the square "DIN" dies. The Molex UP60, order number 638018900 will process the square "DIN" style die sets with the 638018901 adapter. The Molex 12 ton battery crimp tool, order number 638161000 will process the square "DIN" style die sets with the 638161100 adapter. Refer to the appropriate crimper instruction manual for installation and operation information. Type: DIN KIT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Crimp Module
UPC	887191540832
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents ATS-640080770-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207129 Series](#)

**Use With**

UP60 Air Crimp Press for Loose Product [638018900](#) , [638018901](#) or Battery Powered Crimping Tool [638161000](#) , [638161100](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64008-0770](#)